

Eaton 086348

Catalog Number: 086348

Eaton Moeller® series RMQ16 Illuminated pushbutton actuator, blue, maintained, +filament lamp 24V Q18LTR-BL/WB

General specifications



Product Name

Eaton Moeller® series RMQ16
Illuminated pushbutton actuator

Catalog Number

086348

EAN

4015080863489

Product Length/Depth

59 mm

Product Height

18 mm

Product Width

18 mm

Product Weight

0.009 kg

Certifications

UL File No.: E29184

CSA

CSA-C22.2 No. 14-05

CE

UL 508

IEC/EN 60947-5

IEC/EN 60947

UL

UL Category Control No.: NKCR

CSA File No.: 46552

CSA Class No.: 3211-03

Product specifications

Type

Illuminated pushbutton actuator

Actuator color

Blue

Actuator function

Switching function latching

Maintained

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Please enquire

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

Resources

Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004136.pdf](#)

[DA-DC-00004158.pdf](#)

Drawings

[eaton-operating-pushbutton-rmq16-dimensions-002.eps](#)

[eaton-operating-button-rmq16-symbol.eps](#)

eCAD model

[ETN.086348.edz](#)

Installation instructions

[IL04716016Z](#)

mCAD model

[leuchtdruck_18.stp](#)

[DA-CS-druck_18](#)

[DA-CD-druck_18](#)

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

Filament bulb (24 V)

Operating frequency

1800 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Connection to SmartWire-DT

No

Actuating force

4 N

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

25 °C

Equipment heat dissipation, current-dependent Pvid

0 W

Heat dissipation capacity Pdis

0 W

Heat dissipation per pole, current-dependent Pvid

0 W

Number of command positions

1

Opening diameter

16 mm

Opening height

0 mm

Rated insulation voltage (Ui)

250 V

Rated operational current for specified heat dissipation (In)

0 A

Rated operational voltage (Ue) at AC - max

24 V

Rated impulse withstand voltage (Uimp)

800 V AC

Bezel color

Black

Shock resistance

Mechanical, According to IEC/EN 60068-2-27

40 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal
shock 11 ms

Bezel material

Plastic

Terminal capacity

0.5 - 1.0 mm²

Design

Flat

Mounting position

As required

Terminal size

2.8 x 0.8 mm to DIN 46244, Blade terminal

2.8 x 0.8 mm to DIN 46247 and IEC 60760, Fast-on connectors

Overvoltage category

III

Control circuit reliability

1 failure per 10,000,000 switching operations (Statistically determined, at 24 V DC/5 mA)

1 failure per 5,000,000 switching operations (statistically determined, at 5 V DC/1 mA)

Degree of protection

IP65

NEMA 1

Degree of protection (front side)

IP65

NEMA 1

Inscription

Blank

Front element type

Flat

Lens type

Square

Lifespan, mechanical

30,000,000 Operations

Static heat dissipation, non-current-dependent P_{vs}

1 W

Width opening

0 mm

Product category

RMQ16

Size

Front dimensions: 18 x 18 mm

Suitable for

Illumination



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)