



### Main

Range	TeSys
Device short name	LUA1
Product or component type	Auxiliary contact

### Complementary

Auxiliary contact composition	2 NO
Signalling function	Fault signalling Indicating rotary knob in ready position
[Ue] rated operational voltage	<= 250 V AC <= 250 V DC
[Ui] rated insulation voltage	250 V conforming to CSA 250 V conforming to IEC 60947-5-1 250 V conforming to UL
[Ith] conventional free air thermal current	2.5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Product weight	0.03 kg
Connections - terminals	Screw clamp terminals

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0721 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---