




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Coverpart Kit**

Number of Positions: **8**

Operating Temperature (Max): **85 °C [ 185 °F ]**

Operating Temperature Range: **-20 – 85 °C [ -4 – 185 °F ]**

Features

Product Type Features

Sealable	No
Connector Cover Type	Strain Relief Coverpart Kit

Configuration Features

Number of Positions	8
---------------------	---

Housing Features

Compatible With Connector Shape	Rectangular
---------------------------------	-------------

Usage Conditions

Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025  
(247)  
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 794617-8  
8POS,MICRO MNL,RCPT HSG


Customers Also Bought




TE Part #YCTJ-3A-03C0160000  
RAIL ASSY



TE Part #YCTJ-3A-02C0160000  
RAIL ASSY



TE Part #65002-06N  
RECP ASSY



TE Part #2178415-1  
MJ,RJ45,SMT,SHLD





TE Part #3-1734506-0

RCPT, 2.0MM, 14P,VRT MT, 8 Au", 2.6 ST


TE Part #CTS-S20-20

CONT SOC ASSY



TE Part #YCTJ122E05EC015000

MODULE ASSY




TE Part #1-2314822-2

12P,2MM,B-B,REC,DRV,T,2.7,0.76AU,TB



TE Part #YCTJ122E02DC015000

ELEC MODULE



TE Part #CTJ920E06N-513

RECP ASSY

Documents

Product Drawings

8 pos. coverpart (kit) for P/N 794616-8

English

Product Specifications

Application Specification

English