S SCHMERSAL

EN	Operating instructions Original	.pages	1 t	0.	6
----	---------------------------------	--------	-----	----	---

\sim	-	-	m

1 /	About this document
1.1	=unction
1.2	Target group: authorised qualified personnel
	Explanation of the symbols used
	Appropriate use
	General safety instructions
	Warning about misuse
	Exclusion of liability
	· · · · · · · · · · · · · · · · · · ·
2	Product description
	Ordering code
	Special versions2
	Destination and use
	Technical data
	Safety classification
2.0	suicty diagonious in the second secon
3	Mounting
	General mounting instructions
	Dimensions
J.Z 1	iniensions
4	Electrical connection
	General information for electrical connection
7.1	Deficial information for electrical confidention
5 (Operating principle and settings
	_ED functions
	Description of the terminals
	Notes4
5.5	voies
6	Sat up and maintanance
	Set-up and maintenance
	Functional testing
0.2	Maintenance
-	Diagonombly and diagonal
	Disassembly and disposal
	Disassembly
1.2	Disposal

8	Αpı	pen	dix
•	, .P	,,,,	

8.1	Wiring examples	. 4
	Sensor configuration	
	Actuator configuration	
R 4	Flow diagram	F

EU Declaration of conformity

1. About this document

1.1 Function

This operating instructions manual provides all the information you need for the mounting, set-up and commissioning to ensure the safe operation and disassembly of the safety-monitoring module. The operating instructions must be available in a legible condition and a complete version in the vicinity of the device.

1.2 Target group: authorised qualified personnel

All operations described in this operating instructions manual must be carried out by trained specialist personnel, authorised by the plant operator only.

Please make sure that you have read and understood these operating instructions and that you know all applicable legislations regarding occupational safety and accident prevention prior to installation and putting the component into operation.

The machine builder must carefully select the harmonised standards to be complied with as well as other technical specifications for the selection, mounting and integration of the components.

1.3 Explanation of the symbols used



Information, hint, note:

This symbol is used for identifying useful additional information.



Caution: Failure to comply with this warning notice could lead to failures or malfunctions.

Warning: Failure to comply with this warning notice could lead to physical injury and/or damage to the machine.

1.4 Appropriate use

The products described in these operating instructions are developed to execute safety-related functions as part of an entire plant or machine. It is the responsibility of the manufacturer of a machine or plant to ensure the correct functionality of the entire machine or plant.

The safety-monitoring module must be exclusively used in accordance with the versions listed below or for the applications authorised by the manufacturer. Detailed information regarding the range of applications can be found in the chapter "Product description".

1.5 General safety instructions

The user must observe the safety instructions in this operating instructions manual, the country-specific installation standards as well as all prevailing safety regulations and accident prevention rules.



Further technical information can be found in the online catalogue on the Internet: www.schmersal.net.

The information contained in this operating instructions manual is provided without liability and is subject to technical modifications.

There are no residual risks, provided that the safety instructions as well as the instructions regarding mounting, commissioning, operation and maintenance are observed.

1.6 Warning about misuse



In case of inadequate or improper use or manipulations of the safety-monitoring module, personal hazards or damage to machinery or plant components cannot be excluded. The relevant requirements of the standards ISO 14119 and ISO 13850 must be observed.

1.7 Exclusion of liability

We shall accept no liability for damages and malfunctions resulting from defective mounting or failure to comply with this operating instructions manual. The manufacturer shall accept no liability for damages resulting from the use of unauthorised spare parts or accessories.

For safety reasons, invasive work on the device as well as arbitrary repairs, conversions and modifications to the device are strictly forbidden; the manufacturer shall accept no liability for damages resulting from such invasive work, arbitrary repairs, conversions and/or modifications to the device.

The safety-monitoring module must only be used when the enclosure is closed, i.e. with the front cover fitted.

2. Product description

2.1 Ordering code

This operating instructions manual applies to the following types:

SRB201ZH -24VDC



Only if the information described in this operating instructions manual are realised correctly, the safety function and therefore the compliance with the Machinery Directive is maintained.

2.2 Special versions

For special versions, which are not listed in the order code below 2.1, these specifications apply accordingly, provided that they correspond to the standard version.

2.3 Destination and use

The safety-monitoring modules for integration in safety circuits are designed for fitting in control cabinets. They are used for the safe evaluation of the signals of two actuating elements A + B and correspond to a type III/C two-hand control to EN 574.

The safety function is defined as the opening of the enabling circuits 13-14 and 23-24 when one or both actuating elements A + B are released. The safety-relevant current paths with the output contacts 13-14 and 23-24 meet the following requirements under observation of a PFH value assessment (also refer to chapter 2.5 "Safety classification"):

- Control category 4 PL e to ISO 13849-1
- corresponds to SIL 3 to IEC 61508-2
- SILCL 3 to EN 62061

To determine the Performance Level (PL) to ISO 13849-1 of the entire safety function (e.g. sensor, logic, actuator), an assessment of all relevant components is required.



The entire concept of the control system, in which the safety component is integrated, must be validated to the relevant standards.

2.4 Technical data

General data	
Standards:	EN 60204-1, IEC 60947-5-1;
	ISO 13849-1, IEC 61508
Climate resistance:	EN 60068-2-78
	s onto standard DIN rail to EN 60715
Terminal designations:	IEC 60947-1
Material of the housings:	Plastic, glass-fibre reinforced thermoplastic, ventilated
Material of the contacts:	AgSnO, self-cleaning, positive drive
Weight:	200 g
Start conditions:	Automatic
Feedback circuit (Y/N):	yes
Pull-in delay for automatic start:	typ. 50 ms
Response time:	typ. 30 ms, max. 37 ms
Bridging in case of voltage drops:	typ. 30 ms
Simultaneity monitoring:	±yp. 00 ms
Mechanical data	= 0.5 \$
Connection type:	Screw connection
Cable section:	min. 0.25 mm² / max. 2.5 mm²
Connecting cable:	rigid or flexible
Tightening torque for the terminals:	0.6 Nm
With removable terminals (Y/N):	
Mechanical life:	yes 10 million operations
Electrical life:	Derating curve available on request
Resistance to shock:	30 g / 11 ms
Resistance to vibrations to EN 6006	68-2-6: 10 55 Hz,
Resistance to vibrations to EN 6000	amplitude 0.35 mm
Ambient conditions	ampiliado oldo IIIII
Ambient temperature:	−25 °C +60 °C
Storage and transport temperature:	−40 °C +85 °C
Protection class:	Enclosure: IP40
	Terminals: IP20
	Clearance: IP54
Air clearances and creepage distan	ces
to IEC 60664-1:	4 kV/2 (basic insulation)
EMC rating:	to EMC Directive
Electrical data	
Contact resistance in new state:	max. 100 mΩ
Power consumption:	max. 1.2 W
Rated operating voltage U _e :	24 VDC -10%/+10%,
	residual ripple max. 10%
Fuse rating for the operating voltage	e: Internal electronic trip:
	F1, F2: tripping current > 0.2 A
	F3: tripping current > 0.6 A
Monitored inputs	•
Cross-wire detection (Y/N):	Yes
Wire breakage detection (Y/N):	Yes
Earth leakage detection (Y/N):	Yes
Number of NO contacts:	2
Number of NC contacts:	2
Cable length:	1,500 m with1.5 mm ²
Ü	2,500 m with2.5 mm ²
Conduction resistance:	max. 40 Ω

Operating instructions Safety-monitoring module

Outputs

Number of safety contacts: 2 (13-14; 23-2		
1 (31-32)	Number of auxiliary contacts:	
0	Number of signalling outputs:	
s: max. 250 V, 6 A ohmic	Switching capacity of the safety contact	
(inductive in case of		
appropriate protective wiring);		
min. 10 V / 10 mA		
acts: 24 VDC / 2 A	Switching capacity of the auxiliary conta	
external (I _k = 1000 A)	Fuse rating of the safety contacts:	
to IEC 60947-5-1		
Safety fuse 8 A quick blow,		
6.3 A slow blow		
2.5 A quick blow, 2 A slow blow	Fuse rating for the auxiliary contacts:	
AC-15: 230 V / 6 A	Utilisation category to IEC 60947-5-1:	

Dimensions H x W x D: $100 \times 22.5 \times 121 \text{ mm}$ The data specified in this manual are applicable when the component is operated with rated operating voltage $U_a \pm 0\%$.

2.5 Safety classification

Standards:	ISO 13849-1, IEC 61508
PL:	up to e
Control category:	up to 4
DC:	99% (high)
CCF:	> 65 points
PFH:	≤ 2.00 × 10 ⁻⁸ /h
SIL:	up to 3
Service life:	20 years

The PFH value of 2.00×10^{-8} /h applies to the combinations of contact load (current through enabling contacts) and number of switching cycles ($n_{op/y}$) mentioned in the table below. At 365 operating days per year and a 24-hours operation, this results in the below-mentioned switching cycle times (t_{cycle}) for the relay contacts. Diverging applications upon request.

Contact load	$\mathbf{n}_{op/y}$	t _{cycle}
20 %	525,600	1.0 min
40 %	210,240	2.5 min
60 %	75,087	7.0 min
80 %	30,918	17.0 min
100 %	12,223	43.0 min

3. Mounting

3.1 General mounting instructions

Mounting: snaps onto standard DIN rails to EN 60715.

Snap the bottom of the enclosure slightly tilted forwards in the DIN rail and push up until it latches in position.

3.2 Dimensions

All measurements in mm.

Device dimensions (H/W/D): 100 x 22.5 x 121 mm with plugged-in terminals: $120 \times 22.5 \times 121$ mm

4. Electrical connection

4.1 General information for electrical connection



The electrical connection may only be carried out by authorised personnel in a de-energised condition.



As far as the electrical safety is concerned, the protection against unintentional contact of the connected and therefore electrically interconnected apparatus and the insulation of the feed cables must be designed for the highest voltage, which can occur in the device.



DC-13: 24 V / 6 A

To avoid EMC disturbances, the physical ambient and operational conditions at the place where the product is installed, must meet the provisions laid down in the paragraph "Electromagnetic Compatibility (EMC)" of DIN EN 60204-1.

Wiring examples: see appendix

5. Operating principle and settings

5.1 LED functions

K1: Status channel 1 K2: Status channel 2

5.2 Description of the terminals

Voltages:	A1	+24 VDC
	A1.1	+ 24 V
	A2	0 VDC
	A2.1	0 V
Inputs:	S11	Input channel 1 (+)
	S12	Input channel 1 (-)
	S21	Input channel 2 (-)
	S22	Input channel 2 (+)
Outputs:	13 - 14	First safety enabling circuit
	23 - 24	Second safety enabling circuit
	31 - 32	Auxiliary NC contact as signalling contact
Start:	X1 - X2	Feedback circuit



Fig. 1

5.3 Notes



Signalling outputs must not be used in safety circuits.



The NC contact of the buttons A + B must be opened, before the NO contact closes. No overlapping contacts to avoid triggering of the fuses F1 and F2.



The pushbuttons A + B must be actuated within a timeframe of ≤ 0.5 sec (simultaneous operation monitoring), otherwise no start enabling signal is given!

6. Set-up and maintenance

6.1 Functional testing

The safety function of the safety-monitoring module must be tested. The following conditions must be previously checked and met:

- 1. Correct fixing
- 2. Check the integrity of the cable entry and connections
- 3. Check the safety-monitoring module's enclosure for damage.
- Check the electrical function of the connected sensors and their influence on the safety-monitoring module and the downstream actuators

6.2 Maintenance

A regular visual inspection and functional test, including the following steps, is recommended:

- 1. Check the correct fixing of the safety-monitoring module
- 2. Check the cable for damages
- 3. Check electrical function



If a manual functional check is necessary to detect a possible accumulation of faults, then this must take place during the intervals noted as follows:

- at least every month for PL e with category 3 or category 4 (according to ISO 13849-1) or SIL 3 with HFT (hardware fault tolerance) = 1 (according to IEC 62061);
- at least every 12 months for PL d with category 3 (according to ISO 13849-1) or SIL 2 with HFT (hardware fault tolerance) = 1 (according to IEC 62061).

Damaged or defective components must be replaced.

7. Disassembly and disposal

7.1 Disassembly

The safety-monitoring module must be disassembled in a de-energised condition only.

Push up the bottom of the enclosure and hang out slightly tilted forwards.

7.2 Disposal

The safety-monitoring module must be disposed of in an appropriate manner in accordance with the national prescriptions and legislations.

8. Appendix

8.1 Wiring examples

Dual-channel control with two pushbuttons A and B (see Fig. 2)

- Relay outputs: Suitable for 2-channel control, for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- H2 = Feedback circuit




Fig. 2 a) Logic

8.2 Sensor configuration

Two-hand control to EN 574 and EN 60204-1 (see Fig. 3)

- Malfunctions of every contact as well as earth leakages and cross-wire shorts are detected.
- Feedback circuit (+12):

the feedback circuit is integrated as shown. The safety-technical function of external positive-guided contactors is monitored by a series-wiring of the NC contacts with the terminals X1 and X2. In idle state, this circuit must be closed. If the feedback circuit is not required, establish a bridge.


- · Safety category III/C to EN 574
- Category 4 PL e to ISO 13849-1 possible.

Two-hand control to EN 574 and EN 60204-1 (see Fig. 4)

- Malfunctions of every contact as well as earth leakages and crosswire shorts are detected.
- Feedback circuit (+2):

the feedback circuit is integrated as shown. The safety-technical function of external positive-guided contactors is monitored by a series-wiring of the NC contacts with the terminals X1 and X2. In idle state, this circuit must be closed. If the feedback circuit is not required, establish a bridge.

- · Safety category III/C to EN 574
- Category 4 PL e to ISO 13849-1 possible.






Fig. 3

Fig. 4

8.3 Actuator configuration

Single-channel control with feedback circuit (Fig. 5)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- • ⊕ = feedback circuit:
 If the feedback circuit is not required, establish a bridge.

Dual-channel control with feedback circuit (Fig. 6)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- e = feedback circuit:
 If the feedback circuit is not required, establish a bridge.




Fig. 5 Fig. 6

Differential control with feedback circuit (see Fig. 7)

- Suitable for increase in capacity or number of contacts by means of contactors or relays with positive-guided contacts.
- (H2) = feedback circuit:

If the feedback circuit is not required, establish a bridge.




Fig. 7 a) Enabling signal controller

8.4 Flow diagram




Fig. 8

Key

- 1) uninterrupted workcycle;
- 2) Fault in feedback circuit;
- 3) Synchronous actuation fault t > 0.5 s
- 4) Fault button A, B before UBin;
- A) Operating voltage UB;
- B) Two-hand button A: the representation is related to the potentials at the terminals of the safety-monitoring module;
 - a) NC contact S11; b) NO contact S12;
- C) Two-hand button B: the representation is related to the potentials at the terminals of the safety-monitoring module;
 - c) NC contact S21; d) NO contact S22;
- D) Simultaneity monitoring ts (synchronous actuation);
- E) Feedback circuit X1-X2;
- F) Output contacts 13-14, 23-24 potential-free

9. EU Declaration of conformity

EU Declaration of conformity

9 SCHMERSAL

Original K.A. Schmersal GmbH & Co. KG

Möddinghofe 30 42279 Wuppertal Germany

Internet: www.schmersal.com

We hereby certify that the hereafter described components both in their basic design and construction conform

to the applicable European Directives.

Name of the component: SRB201ZH -24VDC

Description of the component: Safety switchgear for two-hand applications

Relevant Directives: Machinery Directive

EMC-Directive 2014/30/EU RoHS-Directive 2011/65/EU

Applied standards: EN 574:1996 + A1:2008,

ISO 13851:2002, EN ISO 13849-1:2015, EN ISO 13849-2:2012, IEC 61326-3-1:2017

Notified body for the prototype test: TÜV Rheinland Industrie Service GmbH

Alboinstr. 56, 12103 Berlin

ID n°: 0035

01/205/5316.01/18 EC-prototype test certificate:

Person authorised for the compilation

Oliver Wacker Möddinghofe 30 of the technical documentation:

42279 Wuppertal

Place and date of issue: Wuppertal, July 12, 2018

SRB201ZH-24VDC-F-EN

Authorised signature Philip Schmersal Managing Director



The currently valid declaration of conformity can be downloaded from the internet at www.schmersal.net.





Möddinghofe 30, D - 42279 Wuppertal Postfach 24 02 63, D - 42232 Wuppertal

Phone: +49 - (0)2 02 - 64 74 - 0 Telefax: +49 - (0)2 02 - 64 74 - 1 00 info@schmersal.com E-Mail: Internet: http://www.schmersal.com