



Heavy Duty Lever End Cutting Nipper PowerBolt

- | Specifically geared towards the requirements in the building and manufacturing industry
- | Precision cutting edge for bolts, nails, rivets, hard wires and similar materials
- | Asymmetrical cutting edge for easily cutting long workpieces, too
- | Cutting edges inductively hardened
- | Tremendous cutting performance, up to 50 % power saving compared with conventional end cutting pliers
- | Power transmission with optimum leverage for easy and effortless work
- | Handles coated with plastic
- | Made of special tool steel, forged, oil-hardened

SKU: 1311-12-200-SB

Safety Notes



Use tools for indicated purposes only.
Before using the cutting tools please wear body protection such as safety mask, safety glasses and hand protection.
Beware of wire ends flying off!

General Information

End Cutting Nipper

These end cutting nippers are drop-forged from tool steel and additionally oil hardened, they have induction-hardened cutters that allow you to cut both hard and soft wires with ease. The cutters are also suitable for use as steel fixer's pincers and for tying wire mesh.



Low-effort construction work

It takes many hours of hard manual work to erect the steel framework for a building. Tools that are both tough and strain-reducing are an essential feature of construction work. Bolt-cutters, steel fixer's pincers and end cutting nippers made by NWS provide easy handling and save tremendously on the effort required when cutting through reinforcing matting or twisting reinforcing wire. This makes work easier and quicker – which benefits construction progress at the same time.

Downloads

	1311-12-200.jpg		detail_1311-12-200_0909241717.jpg		detail_1311-12-200_0909241707.jpg
	detail_1311-12-200_0909231602.jpg		detail_1311-12-200_0909241712.jpg		VP-1435.jpg

Technical Data

1311-12-200-SB		
	Length - mm	200
	Length - in	8
	Cutting edge shape	
	Soft wire (220 N/mm ²) copper, aluminium, plastic - cutting capacity - Ø mm	4,5
	Medium hard wire (750 N / mm ²) nail, wire nail - cutting capacity - Ø mm	4
	Hard wire (1800 N / mm ²) wire rope fiber, steel rope - cutting capacity - Ø mm	3,5
	Round steel (1200 N/mm ²) - cutting capacity - Ø mm	4
	Cutting edge hardness - HRC	61 - 63
	Weight - g	360
	Length including self-service packaging - mm	245
	Width including self-service packaging - mm	65
	Height including self-service packaging - mm	30
	Weight self-service packaging - g	15
	Packing unit	6
	Barcode	40 03758 63113 3