






1		2		3		4		5		6	
ITEM #	PART #	REV	DESCRIPTION	QTY	Material	Weight					
1	MDA050	01	Nozzle body	1	Aluminium	10.4g					
2	PA6058	02	Std. Spray Valve Assy. - 1.5mm	1		6.4g					
3	PA6057	03	Std. Angle Spray Valve Cap	1	Aluminium	9.8g					
4	FOZ005	02	O Ring	1	Viton	0.1g					






SECTION A-A

REL-03	FOZ028 & FOZ005 'O' Rings were removed to stop problems with air flow.	27/11/2009
REV.	DESCRIPTION	DATE

 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHTS ARE RESERVED.	MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1
	FINISH		DATE				SHEET 1 OF 2
	COLOUR		ECR No.	00036	TITLE		Std. Spray Nozzle Assy - 1.5mm
	NOTES						
						DWG. No.	MPN - PA6061
					A4		03

	1	2	3		4	5	6				
A	Technical data										
	Type	Hot melt applicator nozzle									
	Material composition	Aluminium, steel, music wire, viton rubber									
	Weight	26.7g (0.94 oz)									
	Thread size	3/8 UNF									
	Nozzle hole size	1.5mm (0.06")									
	Spring rate	0.73 N/mm (4.15 lb/inch)									
B											
C											
D	 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS DESIGNS AND COPYRIGHTS ARE RESERVED.		MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1		
			FINISH		DATE						
			COLOUR		ECR No.	00036			SHEET 2 OF 2		
			NOTES			TITLE					
						Std. Spray Nozzle Assy - 1.5mm					
					DWG. No.		PA6061	REVISION			
					A4			03			
	1	2	3		4	5	6				

