

The trusted value of OSRAM Digital Systems continues with Inventronics Global – where experience meets innovation.

## PL-CN50-COB -1000-TW-90-40D-G3

PL COIN 50 COB TW G3 | Spot-, Down- and Wallmount Light Engines and Modules



### Product family features

- Color consistency in 3 SDCM
- High flux output up to 1155 lm
- Beam angle: 24°, 40°
- Type of protection: IP20

### Product family benefits

- Compatible with conventional MR16 lamps
- Wide CCT range from 2700 K to 6500 K
- Precise optical control and free from multi-shadow issue

## Areas of application

- Retail, shop, restaurant, hospitality
- High-end residential
- Suitable for indoor applications
- Connecting multiple modules in parallel on one LED driver is not permitted
- Connecting multiple modules in series on one LED driver is not recommended
- Do not use in sealed fixtures
- Avoid covering the lens with dust or any object

## Technical data

### Electrical data

Nominal current	0.3 A
Type of current	DC
On-mode power	10.1 W
Energy consumption in on-mode	10.1 kWh/1000h
Maximum forward voltage	38 V

### Photometrical data

Luminous efficacy	99 lm/W
Peak luminous intensity	2370
Correlated color temperature CCT	4000 K
Colour consistency (McAdam ellipses)	3
Useful luminous flux ( $\Phi_{use}$ )	1089 lm
Color rendering index Ra	90

### Light technical data

Beam angle	40 °
Starting time	0 s
Warm-up time (60 %)	0 s

### LED module information

Number of LEDs per module	1
---------------------------	---

## Dimensions & weight

Product weight	94.00 g
Height EPREL	55 mm
Length EPREL	50 mm
Width EPREL	50 mm

## Temperatures & operating conditions

Performance temp. acc. to IEC 62717	70 °C
Maximum temperature at tc test point	95 °C

## Lifespan

Number of switching cycles	>15000
Lumen maintenance factor LMF	96
L70B50 lifetime	50000 h

## Additional product data

Lighting technology used	LED
--------------------------	-----

## Capabilities

Dimmable	Yes
----------	-----

## Certificates & standards

<b>Standards</b>	IEC 62778 / IEC 61347-1 / EN 62031 / IEC 60598-1 / EN 55015 / EN 61547
<b>Type of protection</b>	IP20
<b>Energy efficiency class</b>	E

## Logistical data

<b>Commodity code</b>	85395100000
-----------------------	-------------

## Environmental information

<b>Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)</b>	
<b>Date of Declaration</b>	13-01-2026
<b>Primary Article Identifier</b>	6937186151698
<b>Declaration No. in SCIP database</b>	In work
<b>SCIP_ID</b>	

## Download Data

File		
Certificates	PDF	▶ CB CERTIFICATE 331284_70044 PL COIN 35 50 111 G3
Certificates	PDF	▶ PL ENEC 40031612 05082025
User instruction	PDF	▶ UI PL-CN50 111 COB TW G3

## Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
6937186151698 INVENTRONICS	PL-CN50-COB -1000- TW-90-40D-G3	Shipping carton box 20 Pieces	268 x 110 x 138 mm	4.07 dm <sup>3</sup>	107.33 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit