

## | IWPT SERIES

### INDUSTRIAL WIRELESS PRESSURE TRANSDUCER



### Typical Applications Include

- Simple cable replacement installation
- dispense with expensive cable runs
- Environmental monitoring
  - pumping stations, sewage plants, water treatment
- Facilities management
  - boiler rooms, plant hydraulics, plant pneumatics
- Asset monitoring
  - tanks farms, process plants, HVAC and building management
- Service Contract
  - temporary installation for servicing and field trials

The IWPT Wireless Pressure Transducer is a cost effective replacement to a traditionally wired pressure transducer that offers the advantages of a low-cost installation in inaccessible and expensive installation environments

It is easily paired to any of the range of IWR receivers - thus offering a "plug and play" solution to your pressure measurement applications.

The instrument uses a piezo-resistive ceramic sensor mounted within a 316 stainless steel housing giving excellent media compatibility for the harshest of applications. A swivel adapter is available which allows the head to be easily aligned to the IWR receiver - see IWPT-SA.

The IWPT sensor can be used with any of the IWR range of receivers. A line-of-sight range of up to 500 m is possible depending on the wireless receiver used (refer to specific receiver data sheets for further information).

Each device is temperature compensated, calibrated and supplied with a traceable serial number.

### **Features**

- Pressure ranges from -1 to +400 bar gauge
- Up to 500 m line-of-site range (depending on receiver)
- Piezo-resistive thick film ceramic sensor with stainless steel body
- Five year battery life at 10 second transmission update rate
- Simple DIL switch pairing with the single or five channel receiver
- Single, five and multi-channel channel receivers available (up to 128)
- User-selectable transmission update rates
- Analog, digital, RS-232/485, Ethernet & USB receiver outputs
- Receiver clean contacts provide process alarm functions
- Suitable for liquids and gases



### Transmitter Output

*Transmission Frequency	2.4 Ghz using ISM bands		
Transmit Power	18 dBm		
System Channel	User selectable via DIL switch		
Antenna	Integral OdBi		

<sup>\*</sup>Compliant with EN 300 328, V1.8.1

### System Performance

Accuracy (Non-linearity & Hysteresis)	<±0.25% /FS (BFSL)
Setting Errors (offsets)	Zero & Full Scale, <±0.5% /FS

# **Material Specifications**

Pressure Housing	316 Stainless Steel	
"O" Ring Seals	Viton	
Diaphragm	Ceramic Al <sub>2</sub> O <sub>3</sub> 96%	
Wireless Enclosure Material	rial Plastic	
Weight	310g including battery	
**Installation Position	Any	
Environmental Protection  Designed to IP68 (not recommended for submersion due to signal loss		
** Consult installation manual to ensure adequate signal path between transmitter		

# **Instrument Power Source**

Battery Type	User replaceable Lithium C cell
Battery Life	Five years at 10 second update rate
Battery Shelf Life	10 years

# **Receiver Output Signals**

and receiver.

Receiver Part Number	Receiver Outputs
IoT Gateway	Built-in cellular modem allows all data to be sent to remote servers
IWR-PORT	RS-232 or RS-485 or Ethernet MODBUS Communications. Up to 128 off analog 4-20 mA or Relay outputs can be obtained by fitting extra ISOSLICE I/O modules
IWR-USB	Displays & Logs data on any PC running IWR- USB software
IWR-5	5 off 4-20 mA or 1-5 V dc and 1 Relay output
IWR-1	1 off 4-20 mA and 1-5 V dc and 1 Relay output

- \*\*\*Transmission Update Rate 1, 5, 10 and 30 seconds \*\*\* Consult installation manual for set-up:
- Single channel system is DIL switch configurable
- Five channel system requires set-up using "IWR Set" user software

### **Environmental Conditions & Thermal Effects**

Media Temperature	-20°C to +135°C
Ambient Temperature	-20°C to +50°C
Storage Temperature	-20°C to +80°C
Humidity	5% to 95% RH non-condensing
Thermal Zero Shift	<±0.04% /FS/°C
Thermal Span Shift	<±0.02% /°C typical

### **Mechanical Stability**

See user manual




### **Transmitter**

Nominal Pressure, Gauge	bar	1	2	5	10	20	50	100	250	400
Compound Range, Gauge	bar	-1 to 0	-1 to 2	-1 to 5	-1 to 9	-1 to 19	-1 to 24			
Permissible Overpressure	bar	2	4	10	20	40	100	200	400	650
Burst Pressure	bar	4	5	12	25	50	120	250	500	650



#### All dimensions are in millimeters.





Pressure Transducer	See table below
Spare Battery	IBAT-1
Receivers	See IoT Gateway, IWR-1, IWR-5, IWR-PORT and IWR-USB data sheets
Five Channel Configuration Software*	IWR-Set
Swivel Adapter	IWPT-SA

<sup>\*</sup>Download free user configuration software here: https://www.cynergy3.com/sites/default/files/IWR-Set\_v2.4\_installer.zip

	$\Lambda \Lambda \Lambda \Lambda$	

Part Number	Pressure Rating
IWPT-G1000-00	0 - 1 Bar G
IWPT-G6000-00	0 - 6 Bar G
IWPT-GM1P9-00	-1 to +9 Bar G
IWPT-G1002-00	0 - 10 Bar G
IWPT-G1602-00	0 - 16 Bar G
IWPT-C0184-00	-1 to +24 Bar G
IWPT-G2502-00	0 - 25 Bar G
IWPT-G4002-00	0 - 40 Bar G
IWPT-G1003-00	0 - 100 Bar G
IWPT-G2503-00	0 - 250 Bar G
IWPT-G4003-00	0 - 400 Bar G

Made in the UK

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at <a href="https://www.sensata.com">www.sensata.com</a> SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

#### **CONTACT US**

EUROPE +44 (0)1202 897969 c3w\_sales@sensata.com Cynergy3 Components Ltd. 7 Cobham Road, Ferndown Industrial Estate, Wimborne, Dorset, BH21 7PE, United Kingdom

USA

+1 310 561 8092 / +1 866 258 5057 c3w\_sales@sensata.com