

特点

- 提供各种螺纹尺寸
- 高质量螺纹设计
- 头高度等于柄直径
- 比不锈钢更加经济

RS Pro 5 . 5 x 12mm 内六角带帽螺钉，黑色，本色钢

RS 号： 281-653



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与领先品牌相当的质量、而无需支付高昂的价格。

商品描述属性

RS PRO 的一系列窄头沉头螺丝，适用于难以触及的区域。此类螺丝在机器维修和维护应用中大有用武之地，尤其是当插孔位于狭小的缝隙中时。由于采用高强度钢制成，它们是完美之选，令环境腐蚀不会成为问题。所有型号均高度可靠且质量极佳。

一般规格

螺纹尺寸	M2.5
头部形状	六角套筒盖
材料	钢
表面	黑色、本色
螺纹类型	公制
应用	木材加工、家用应用、紧固件和固定件、机器工具和维修、安全防护、面板制造

机械规格

长度	16mm
不锈钢类型	
螺距	0.45mm
头直径范围	4.32 毫米至 4.68 毫米
头部高度范围	2.36mm 至 2.50mm
钥匙尺寸标称范围	2.02mm 至 2.06mm
关键敬业度	8mm

认证

合规性 / 认证 rohs 符合性证书, DIN7991 , ISO10642 , ansi B18

Please view our full range listing below for all High-Tensile Steel Black Self-Colour Hexagon Socket Cap Head Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Steel	M1.4	6 mm	293246
Hex Socket Cap	Steel	M1.6	3 mm	293252
Hex Socket Cap	Steel	M1.6	6 mm	293268
Hex Socket Cap	Steel	M2	4 mm	293274
Hex Socket Cap	Steel	M2	6 mm	293280
Hex Socket Cap	Steel	M2	12 mm	293296
Hex Socket Cap	Steel	M2.5	4 mm	293303
Hex Socket Cap	Steel	M2.5	6 mm	281647
Hex Socket Cap	Steel	M2.5	12 mm	281653
Hex Socket Cap	Steel	M3	6 mm	4679773
Hex Socket Cap	Steel	M3	8 mm	4679789
Hex Socket Cap	Steel	M3	10 mm	4679795
Hex Socket Cap	Steel	M3	12 mm	4679802
Hex Socket Cap	Steel	M3	15 mm	8229063
Hex Socket Cap	Steel	M3	16 mm	4679818
Hex Socket Cap	Steel	M3	20 mm	4679824
Hex Socket Cap	Steel	M3	25 mm	4679830
Hex Socket Cap	Steel	M3	30 mm	4679846
Hex Socket Cap	Steel	M3	35 mm	8229066
Hex Socket Cap	Steel	M3	40 mm	8229060

Please view our full range listing below for all High-Tensile Steel Black Self-Colour Hexagon Socket Cap Head Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Steel	M4	6 mm	8229079
Hex Socket Cap	Steel	M4	8 mm	4679852
Hex Socket Cap	Steel	M4	10 mm	4679874
Hex Socket Cap	Steel	M4	12 mm	4679880
Hex Socket Cap	Steel	M4	16 mm	4679896
Hex Socket Cap	Steel	M4	20 mm	4679903
Hex Socket Cap	Steel	M4	25 mm	4679919
Hex Socket Cap	Steel	M4	30 mm	4679931
Hex Socket Cap	Steel	M4	35 mm	8229072
Hex Socket Cap	Steel	M4	40 mm	4679947
Hex Socket Cap	Steel	M4	50 mm	8229076

Hex Socket Cap	Steel	M5	8 mm	8229085
Hex Socket Cap	Steel	M5	10 mm	4679953
Hex Socket Cap	Steel	M5	12 mm	4679969
Hex Socket Cap	Steel	M5	16 mm	4679975
Hex Socket Cap	Steel	M5	20 mm	4679981
Hex Socket Cap	Steel	M5	25 mm	4679997
Hex Socket Cap	Steel	M5	30 mm	4680004
Hex Socket Cap	Steel	M5	35 mm	4680010
Hex Socket Cap	Steel	M5	40 mm	4680032
Hex Socket Cap	Steel	M5	50 mm	4680048

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Steel	M6	10 mm	4680054
Hex Socket Cap	Steel	M6	12 mm	4680060
Hex Socket Cap	Steel	M6	14 mm	8229313
Hex Socket Cap	Steel	M6	15 mm	8229085
Hex Socket Cap	Steel	M6	16 mm	4680076
Hex Socket Cap	Steel	M6	20 mm	4680105
Hex Socket Cap	Steel	M6	25 mm	4680082
Hex Socket Cap	Steel	M6	30 mm	4680098
Hex Socket Cap	Steel	M6	35 mm	4680111
Hex Socket Cap	Steel	M6	40 mm	4680127
Hex Socket Cap	Steel	M6	45 mm	4680133
Hex Socket Cap	Steel	M6	50 mm	4680149
Hex Socket Cap	Steel	M6	55 mm	8229082
Hex Socket Cap	Steel	M6	60 mm	4680155
Hex Socket Cap	Steel	M6	70 mm	275018

Hex Socket Cap	Steel	M8	12 mm	529696
Hex Socket Cap	Steel	M8	16 mm	529703
Hex Socket Cap	Steel	M8	20 mm	529719
Hex Socket Cap	Steel	M8	25 mm	529725
Hex Socket Cap	Steel	M8	30 mm	4680161
Hex Socket Cap	Steel	M8	35 mm	4680177
Hex Socket Cap	Steel	M8	40 mm	4680199
Hex Socket Cap	Steel	M8	45 mm	4680206
Hex Socket Cap	Steel	M8	50 mm	4680212
Hex Socket Cap	Steel	M8	55 mm	4680228
Hex Socket Cap	Steel	M8	60 mm	4680234
Hex Socket Cap	Steel	M8	65 mm	8229091
Hex Socket Cap	Steel	M8	70 mm	275052
Hex Socket Cap	Steel	M8	80 mm	4680256
Hex Socket Cap	Steel	M8	100 mm	4680284

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Steel	M10	16 mm	4680262
Hex Socket Cap	Steel	M10	20 mm	4680278
Hex Socket Cap	Steel	M10	25 mm	4680290
Hex Socket Cap	Steel	M10	30 mm	4680313
Hex Socket Cap	Steel	M10	35 mm	4680329
Hex Socket Cap	Steel	M10	40 mm	529810
Hex Socket Cap	Steel	M10	45 mm	275096
Hex Socket Cap	Steel	M10	50 mm	529826
Hex Socket Cap	Steel	M10	55 mm	275103
Hex Socket Cap	Steel	M10	60 mm	529832
Hex Socket Cap	Steel	M10	65 mm	4680335
Hex Socket Cap	Steel	M10	70 mm	4680341
Hex Socket Cap	Steel	M10	80 mm	4680357
Hex Socket Cap	Steel	M10	90 mm	275147
Hex Socket Cap	Steel	M10	100 mm	275153
Hex Socket Cap	Steel	M10	120 mm	4680363

Hex Socket Cap	Steel	M12	25 mm	4680385
Hex Socket Cap	Steel	M12	30 mm	4680391
Hex Socket Cap	Steel	M12	40 mm	4680408
Hex Socket Cap	Steel	M12	45 mm	4680414
Hex Socket Cap	Steel	M12	50 mm	4680420
Hex Socket Cap	Steel	M12	55 mm	275181
Hex Socket Cap	Steel	M12	60 mm	529898
Hex Socket Cap	Steel	M12	65 mm	275197
Hex Socket Cap	Steel	M12	70 mm	275204
Hex Socket Cap	Steel	M12	80 mm	275226
Hex Socket Cap	Steel	M12	90 mm	4680436
Hex Socket Cap	Steel	M12	100 mm	4680442
Hex Socket Cap	Steel	M12	120 mm	4680458

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Steel	M16	40 mm	4680492
Hex Socket Cap	Steel	M16	50 mm	4680515
Hex Socket Cap	Steel	M16	60 mm	275327
Hex Socket Cap	Steel	M16	70 mm	275349
Hex Socket Cap	Steel	M16	80 mm	275361
Hex Socket Cap	Steel	M16	100 mm	275383
Hex Socket Cap	Steel	M16	120 mm	4680543

SOCKET HEAD CAP SCREWS DIN 912/ ISO 4762 / ANSI B 18.3.1 M



Head Diameter d2 max. allows for Knurled Head

Thread Size d1	(M1.4)		M1.6		M2		M2.5		M2.6		M3		M4	
Thread Pitch	0.3		0.35		0.4		0.45		0.45		0.5		0.7	
Thread Length b	14		15		16		17		NA		18		20	
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	2.46	2.74	2.86	3.14	3.62	3.98	4.32	4.68	4.82	5.18	5.32	5.68	6.78	7.22
ISO 4762 (1997)			2.86	3.14	3.62	3.98	4.32	4.68			5.32	5.68	6.78	7.22
ANSI B 18.3.1 M (1986)			2.87	3.14	3.65	3.98	4.33	4.68			5.32	5.68	6.80	7.22
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	1.26	1.40	1.46	1.60	1.86	2.00	2.36	2.50	2.46	2.60	2.86	3.00	3.82	4.00
ISO 4762 (1997)			1.46	1.60	1.86	2.00	2.36	2.50			2.86	3.00	3.82	4.00
ANSI B 18.3.1 M (1986)			1.52	1.60	1.91	2.00	2.40	2.50			2.89	3.00	3.88	4.00
Key Size nominal s	1.3		1.5		1.5		2		2		2.5		3	
	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	1.32	1.36	1.52	1.56	1.52	1.56	2.02	2.06	2.02	2.06	2.52	2.58	3.02	3.08
ISO 4762 (1997)			1.52	1.56	1.52	1.56	2.02	2.06			2.52	2.58	3.02	3.08
ANSI B 18.3.1 M (1986)			1.520	1.545	1.520	1.545	2.020	2.045			2.52	2.56	3.020	3.071
Key Engagement t	min.		min.		min.		min.		min.		min.		min.	
DIN 912 (1983)	0.6		0.7		1		1.10		1.2		1.3		2	
ISO 4762 (1997)			0.7		1		1.10				1.3		2	
ANSI B 18.3.1 M (1986)			0.8		1		1.25				1.5		2	

Thread Size d1	M5		M6		M8		M10		M12		(M14)		M16	
Thread Pitch	0.8		1		1.25		1.5		1.75		2		2	
Thread Length b	22		24		28		32		36		40		44	
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	8.28	8.72	9.78	10.22	12.73	13.27	15.73	16.27	17.73	18.27	20.67	21.33	23.67	24.33
ISO 4762 (1997)	8.28	8.72	9.78	10.22	12.73	13.27	15.73	16.27	17.73	18.27	20.67	21.33	23.67	24.33
ANSI B 18.3.1 M (1986)	8.27	8.72	9.74	10.22	12.70	13.27	15.67	16.27	17.63	18.27	20.6	21.33	23.58	24.33
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	4.82	5.00	5.7	6.0	7.64	8.00	9.64	10.00	11.57	12.00	13.57	14.00	15.57	16.00
ISO 4762 (1997)	4.82	5.00	5.7	6.0	7.64	8.00	9.64	10.00	11.57	12.00	13.57	14.00	15.57	16.00
ANSI B 18.3.1 M (1986)	4.86	5.00	5.85	6.00	7.83	8.00	9.81	10.00	11.79	12.00	13.77	14.00	15.76	16.00
Key Size nominal s	4		5		6		8		10		12		14	
	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	4.020	4.095	5.02	5.14	6.02	6.14	8.025	8.175	10.025	10.175	12.032	12.212	14.032	14.212
ISO 4762 (1997)	4.020	4.095	5.02	5.14	6.02	6.14	8.025	8.175	10.025	10.175	12.032	12.212	14.032	14.212
ANSI B 18.3.1 M (1986)	4.020	4.084	5.020	5.084	6.020	6.095	8.025	8.115	10.025	10.127	12.032	12.146	14.032	14.159
Key Engagement t	min.		min.		min.		min.		min.		min.		min.	
DIN 912 (1983)	2.5		3		4		5		6		7		8	
ISO 4762 (1997)	2.5		3		4		5		6		7		8	
ANSI B 18.3.1 M (1986)	2.5		3		4		5		6		7		8	

Thread Size d1	(M18)		M20		(M22)		M24		(M27)		M30		M33	
Thread Pitch	2.5		2.5		2.5		3		3		3.5		3.5	
Thread Length b	48		52		56		60		66		72		78	
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	26.67	27.33	29.67	30.33	32.61	33.39	35.61	36.39	39.61	40.39	44.61	45.39	49.61	50.39
ISO 4762 (1997)			29.67	30.33			35.61	36.39			44.61	45.39		
ANSI B 18.3.1 M (1986)			29.53	30.33			35.48	36.39			44.42	45.39		
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	17.57	18.00	19.48	20.00	21.48	22.00	23.48	24.00	26.48	27.00	29.48	30.00	32.38	33.00
ISO 4762 (1997)			19.48	20.00			23.48	24.00			29.48	30.00		
ANSI B 18.3.1 M (1986)			19.73	20.00			23.70	24.00			29.67	30.00		
Key Size nominal s	14		17		17		19		19		22		24	
	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	14.032	14.212	17.05	17.23	17.05	17.23	19.065	19.275	19.065	19.275	22.065	22.275	24.065	24.275
ISO 4762 (1997)			17.05	17.23			19.065	19.275			22.065	22.275		
ANSI B 18.3.1 M (1986)			17.050	17.216			19.065	19.243			22.065	22.319		
Key Engagement t	min.		min.		min.		min.		min.		min.		min.	
DIN 912 (1983)	9		10		11		12		13.5		15.5		18	
ISO 4762 (1997)			10				12				15.5			
ANSI B 18.3.1 M (1986)			10				12				15.0			