




**Part Number :** [2149201213](#)

**Product Description :** Pre-Crimped Lead PicoBlade  
Female-to-PicoBlade Female, Tin (Sn) Plating,  
225.00mm Length, 26 AWG, Black

**Series Number :** 214920

**Status :** Active

**Product Category :** Power and Signal Cable  
Assemblies



---

## Documents & Resources


### Drawings

[2149201213 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	214920
Description	Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 225.00mm Length, 26 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	PicoBlade
UPC	193264502400

### Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

### Physical

Cable Length	225.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.569/g
Packaging Type	Bag

Plating min - Mating	0.889µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	26

## Mates With / Use With

### Use with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	<u>51021</u>