



PRODUCT-DETAILS

S803S-C63-R

S803S-C63-R High Performance MCB



General Information	
Extended Product Type	S803S-C63-R
Product ID	2CCS863002R0634
EAN	7612271207205
Catalog Description	S803S-C63-R High Performance MCB
Long Description	The S803S-C63-R is a 3-pole High Performance Circuit breaker with C-characteristic, with ring tongue terminal and a rated current of 63 A. It is a current limiting device with a maximum breaking capacity of 50kA at 240/415V. It can be used for voltages up to 400/690V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S803S-C63-R complies with IEC/EN 60898 -1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S803S-C63-R more comfortable. Due to the fast arc extinction of S803S-C63-R your application will be secured.

ABB EcoSolutions	
ABB EcoSolutions	Yes
EcoSolutions Profile	9AKK108471A1082
Recyclability Rate of the	Design for Closing Resource Loops - Standard EN45555 - 86.29 %

Product acc. to EN45555	
ABB Site Meeting Group	No non-hazardous waste is sent to a landfill
Waste To Landfill Target	
End Of Life	9AKK108470A2575
Disassembling	
Instructions	
Environmental Product	9AKK108470A1695
Declaration - EPD	9AKK108470A1696

Technical

Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(415 V AC) 50 kA (440 V AC) 30 kA (500 V AC) 15 kA (690 V AC) 6 kA (375 V DC) 30 kA
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(415 V AC) 40 kA (440 V AC) 22.5 kA (500 V AC) 11 kA (690 V AC) 4 kA (375 V DC) 30 kA
Contact Position Indication	ON / OFF / TRIP
Energy Limiting Class	3
Electrical Endurance	6000 cycle
Mechanical Endurance	4000 cycle
Number of Protected Poles	3
Number of Poles	3P
Tightening Torque	3.5 N·m 31 in·lb
Release Type	C
Actuator Marking	I / O
Options Provided	Ringlug terminal
Recommended Screw Driver	Pozidriv 2
Accessories Available	Yes
Remarks	Connection from top and bottom Connecting with CU only IP40 in enclosure with cover Cage terminal with captive screw
Connecting Capacity	Flexible 0 ... 50 mm ² Rigid 0 ... 70 mm ²
Terminal Type	Screw Terminals

Electrical

Tripping Characteristic	C
Rated Operational Voltage	acc. to IEC 60898-1 400 V AC acc. to IEC 60947-2 690 V AC
Operational Voltage	Maximum 230/400 V AC Minimum 12 V AC
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 690 V
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Input Voltage Type	AC/DC
Rated Current (I_n)	63 A
Rated Short-Circuit Capacity	(400 V AC) 25 kA

Frequency (f)	50 ... 60 Hz
Rated Frequency (f)	50/60 Hz
Power Loss	19.2 W at Rated Operating Conditions per Pole 6.4 W
Overvoltage Category	IV

Design

Housing Material	Insulation group I, RAL 7035
------------------	------------------------------

Technical UL/CSA

Interrupting Rating acc. to UL1077	(480Y / 277 V AC) 14 kA (600Y / 347 V AC) 6 kA
------------------------------------	---

Material Compliance

RoHS Declaration	2CCC005083D0202
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Date	20211214
REACH Declaration	9AKK108470A9089
REACH Information	False - does not contain substances > 0.1 mass percentage
REACH Date	20250313
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business

Environmental

Ambient Air Temperature	Operation -25 ... +60 °C Storage -40 ... +70 °C
Reference Ambient Air Temperature	acc. to IEC60947-2 30 °C acc. to EN60898-1 30 °C
Degree of Protection	IP20
Pollution Degree	3
Resistance to Vibrations	1 mm 2 - 13.2 Hz 0.7g with Load 100% x 1e 13.2 - 100 Hz
Environmental Information	2CCY413207D0203

Dimensions

Width in Number of Modular Spacings	4.5
Product Net Width	81 mm
Product Net Height	142 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	735 g
Built-In Depth (t ₂)	82.5 mm
Dimension Diagram	2CCC413003C0201

Engineering	
EPLAN Data	9AAC172534_EPLAN

Ordering	
Package Level 1 Units	box 1 piece
Package Level 1 Gross Weight	790 g

Certificates and Declarations	
CB Certificate	9AKK107680A0857
CCC Certificate	9AKK108469A3021
Declaration of Conformity - CE	2CCC005083D0202
DNV GL Certificate	2CCC413018D0201
ESTI Certificate	2CCC413020D0101
KC Certificate	9AKK107680A0932
LR Certificate	2CCC413017D0201
RINA Certificate	2CCC413019D0201
UL Certificate	9AKK107680A2286
VDE Certificate	2CCC413039D0601

Installation	
Instructions and Manuals	2CCC413016M0008
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Mounting Position	Any

Popular Downloads	
Data Sheet, Technical Information	9AKK108468A9560 9AKK108468A9561 9AKK108468A9562

External Classifications and Standards	
ETIM 9	EC000042 - Miniature circuit breaker (MCB)
ETIM 10	EC000042 - Miniature circuit breaker (MCB)
eClass	V11.0 : 27141901
Object Classification Code	F
Standards	IEC/EN 60947-2 IEC/EN 60898-1 UL 1077

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → High Performance Circuit Breakers HPCBs → High Performance Circuit Breakers HPCBs



ABB
Eco
Solutions™