

CP1567 v1.5 RS 764-3017
SAFETY DATA SHEET
RS Pro Ultrasonic Cleaning Liquid

According to Regulation (EC) No 1907/2006, Annex II, as amended. Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	RS Pro Ultrasonic Cleaning Liquid
Product number	764-3017, ZP
UFI	UFI: 44R7-J06P-U004-KM5N

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Cleaning agent.
Uses advised against	No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier	RS Components Ltd Birchington Road, Corby, Northants NN17 9RS +44 (0) 845 850 9900 RCustomerServicesUK@rs-components.com
-----------------	--

	RS Components Ltd Glenview Industrial Estate Herberton Road Rialto Dublin 12 +353 (0) 1 415 3100 enquiries.ie@rs-components.com
--	---

1.4. Emergency telephone number

Emergency telephone	+44 (0)1865 407333 +44 1235 239670
----------------------------	---------------------------------------

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards	Not Classified
Health hazards	Asp. Tox. 1 - H304
Environmental hazards	Not Classified

2.2. Label elements

Hazard pictograms



Signal word	Danger
Hazard statements	H304 May be fatal if swallowed and enters airways.

RS Pro Ultrasonic Cleaning Liquid

Precautionary statements P102 Keep out of reach of children.
P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.
P331 Do NOT induce vomiting.
P501 Dispose of contents/ container in accordance with national regulations.

Contains Alkanes, C11-15-iso-, Alkanes, C9-12-iso-

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Alkanes, C9-12-iso-			30-60%
CAS number: 90622-57-4	EC number: 292-459-0		
Classification			
Flam. Liq. 3 - H226			
Asp. Tox. 1 - H304			
Alkanes, C11-15-iso-			30-60%
CAS number: 90622-58-5	EC number: 292-460-6	REACH registration number: 01-2119456810-40-XXXX	
Classification			
Asp. Tox. 1 - H304			

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information Get medical attention immediately. Show this Safety Data Sheet to the medical personnel.

Inhalation Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Place unconscious person on their side in the recovery position and ensure breathing can take place.

Ingestion Rinse mouth thoroughly with water. Remove any dentures. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Place unconscious person on their side in the recovery position and ensure breathing can take place. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.

Skin contact Rinse with water.

Eye contact Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.

RS Pro Ultrasonic Cleaning Liquid

Protection of first aiders First aid personnel should wear appropriate protective equipment during any rescue. If it is suspected that volatile contaminants are still present around the affected person, first aid personnel should wear an appropriate respirator or self-contained breathing apparatus. Wash contaminated clothing thoroughly with water before removing it from the affected person, or wear gloves. It may be dangerous for first aid personnel to carry out mouth-to-mouth resuscitation.

4.2. Most important symptoms and effects, both acute and delayed

General information See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.

Skin contact Prolonged contact may cause dryness of the skin.

Eye contact May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards Containers can burst violently or explode when heated, due to excessive pressure build-up.

Hazardous combustion products Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

RS Pro Ultrasonic Cleaning Liquid

Personal precautions No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. Ensure procedures and training for emergency decontamination and disposal are in place. Do not touch or walk into spilled material.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Small Spillages: Collect spillage. Large Spillages: Absorb spillage with non-combustible, absorbent material. The contaminated absorbent may pose the same hazard as the spilled material. Collect and place in suitable waste disposal containers and seal securely. Label the containers containing waste and contaminated materials and remove from the area as soon as possible. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store away from incompatible materials (see Section 10). Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage. Bund storage facilities to prevent soil and water pollution in the event of spillage. The storage area floor should be leak-tight, jointless and not absorbent.

Storage class Chemical storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

8.2. Exposure controls

RS Pro Ultrasonic Cleaning Liquid

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Personal, workplace environment or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Use process enclosures, local exhaust ventilation or other engineering controls as the primary means to minimise worker exposure. Personal protective equipment should only be used if worker exposure cannot be controlled adequately by the engineering control measures. Ensure control measures are regularly inspected and maintained. Ensure operatives are trained to minimise exposure.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with European Standard EN166. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with European Standard EN374. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Hygiene measures

Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke. Preventive industrial medical examinations should be carried out. Warn cleaning personnel of any hazardous properties of the product.

Respiratory protection

Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Ensure all respiratory protective equipment is suitable for its intended use and is 'CE'-marked. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with European Standard EN14387. Full face mask respirators with replaceable filter cartridges should comply with European Standard EN136. Half mask and quarter mask respirators with replaceable filter cartridges should comply with European Standard EN140.

Environmental exposure controls

Keep container tightly sealed when not in use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	Characteristic.
Odour threshold	Not available.
pH	pH (concentrated solution): 5-7

RS Pro Ultrasonic Cleaning Liquid

Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	> 60°C Closed cup.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	Not available.
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	1.48 mPa s @ 25°C
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity See the other subsections of this section for further details.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

RS Pro Ultrasonic Cleaning Liquid

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development

Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Asp. Tox. 1 - H304 May be fatal if swallowed and enters airways. Pneumonia may be the result if vomited material containing solvents reaches the lungs.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion

Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.

Skin contact

Prolonged contact may cause dryness of the skin.

Eye contact

May cause temporary eye irritation.

RS Pro Ultrasonic Cleaning Liquid

Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target organs	No specific target organs known.

SECTION 12: Ecological information

Ecotoxicity	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.
--------------------	---

12.1. Toxicity

Toxicity	Based on available data the classification criteria are not met.
-----------------	--

12.2. Persistence and degradability

Persistence and degradability	The degradability of the product is not known.
--------------------------------------	--

12.3. Bioaccumulative potential

Bioaccumulative potential	No data available on bioaccumulation.
----------------------------------	---------------------------------------

Partition coefficient	Not available.
------------------------------	----------------

12.4. Mobility in soil

Mobility	No data available.
-----------------	--------------------

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

Other adverse effects	None known.
------------------------------	-------------

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.
----------------------------	--

Disposal methods	Do not empty into drains. Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labelled with their contents. Incineration or landfill should only be considered when recycling is not feasible.
-------------------------	--

SECTION 14: Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).
----------------	--

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

RS Pro Ultrasonic Cleaning Liquid

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

**Annex II of MARPOL 73/78
and the IBC Code**

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

Health and Safety at Work etc. Act 1974 (as amended).
The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716).
The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"].
EH40/2005 Workplace exposure limits.

EU legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).
Commission Regulation (EU) No 453/2010 of 20 May 2010.
Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).
Dangerous Preparations Directive 1999/45/EC.
Dangerous Substances Directive 67/548/EEC.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

RS Pro Ultrasonic Cleaning Liquid

Abbreviations and acronyms used in the safety data sheet	<p>ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.</p> <p>ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways.</p> <p>RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail.</p> <p>IATA: International Air Transport Association.</p> <p>ICAO: Technical Instructions for the Safe Transport of Dangerous Goods by Air.</p> <p>IMDG: International Maritime Dangerous Goods.</p> <p>CAS: Chemical Abstracts Service.</p> <p>ATE: Acute Toxicity Estimate.</p> <p>LC₅₀: Lethal Concentration to 50 % of a test population.</p> <p>LD₅₀: Lethal Dose to 50% of a test population (Median Lethal Dose).</p> <p>EC₅₀: 50% of maximal Effective Concentration.</p> <p>PBT: Persistent, Bioaccumulative and Toxic substance.</p> <p>vPvB: Very Persistent and Very Bioaccumulative.</p>
Classification abbreviations and acronyms	Asp. Tox. = Aspiration hazard
Classification procedures according to Regulation (EC) 1272/2008	Asp. Tox. 1 - H304: : Calculation method.
Training advice	Read and follow manufacturer's recommendations. Only trained personnel should use this material.
Issued by	Emily Kirk
Revision date	12/11/2019
Revision	3.1
SDS number	757
Hazard statements in full	<p>H226 Flammable liquid and vapour.</p> <p>H304 May be fatal if swallowed and enters airways.</p>

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.