




Switches > Slide Switches



Contact Current Rating: **.4 A**
Configuration (Pole-Throw): **Four Pole - Double Throw**
Product Orientation: **Vertical**
Contact Base Material: **Copper Alloy**
Number of Actuators: **Single**

Features

Configuration Features

Configuration (Pole-Throw)	Four Pole - Double Throw
Number of Actuators	Single
Number of Positions	4
Operating Function	On On

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage	20 VDC

Body Features

Actuator Orientation	Top
Actuator Travel	2.79 mm[.11 in]
Product Orientation	Vertical
Actuator Profile	Flush
Actuator Material	Nylon
Actuator Color	Natural



Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Gold

Termination Features

Termination Post & Tail Length	4.06 mm[.16 in]
Termination Method to PCB	Through Hole - Solder

Dimensions

Product Width	7.35 mm[.289 in]
Product Length	17.78 mm[.7 in]
Actuator Length	.64 mm[.025 in]

Operation/Application

Assembly Process Feature	Auto-Insert Packaging
--------------------------	-----------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Other

Grade	Telecom
-------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1825011-8
ASF22LTR04=DPDT AUTOSLIDE




TE Part # 1825011-2
ASF22G04=DPDT AUTOSLIDE



TE Part # 2-1825011-1
ASF4204=4PDT AUTOSLIDE




TE Part # 2-1825011-4
ASF42RG04=4PDT AUTOSLIDE



TE Part # 1825011-1
ASF2204=DPDT AUTOSLIDE

Also in the Series | Alcoswitch ASE/F



Slide Switches(46)

Customers Also Bought





TE Part #YDTS20W13-08PNV001
RECP ASSY



TE Part #205557-3
AMPLIMITE,RCPT,STD,109,2,KIT



TE Part #3-644456-5
05P MTA100 HDR ASSY (NARROW)



TE Part #5-103166-2
08 MODII HDR DRRA SHRD LF



TE Part #2-2176090-9
RP 1J 0.166W 255K 0.1% 25PPM 1K RL



TE Part #8-2176088-9
RP 1J 0.166W 7K5 0.1% 25PPM 1K RL



TE Part #5-103166-1
06 MODII HDR DRRA SHRD LF



TE Part #3-2176089-7
RP 1J 0.166W 26K7 0.1% 25PPM 1K RL



TE Part #6-2176089-1
RP 1J 0.166W 47K5 0.1% 25PPM 1K RL



TE Part #5-1904006-1
V23234B0001X001-EV-144

Documents

Product Drawings

ASF42G04=4PDT AUTOSLIDE

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-1825011-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1825011-2_C.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-1825011-2_C.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English