

R10-E1Y4-JJ2.5K

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield R10

TE Internal #: 4-1393766-7

General Purpose Signal Relay, DC, Monostable, 4 Form C 4PDT-CO, 3 A Contact Rating, 120 VAC Contact Voltage, .085 W Coil Power, Potter & Brumfield R10

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Signal Relay**

Current Type: **DC**

Coil Magnetic System: **Monostable**

Contact Arrangement: **4 Form C 4PDT-CO**

Contact Current Rating: **3 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Signal Relay
------------------------	------------------------------

Configuration Features

Contact Number of Poles	4
Coil Special Features	Sensitive Version
Contact Arrangement	4 Form C 4PDT-CO

Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts	500 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	1000 Vrms
Contact Switching Load (Min)	100mA @ 12V
Coil Resistance	2500 Ω
Insulation Initial Resistance	10000 MΩ
Contact Current Rating	3 A
Contact Voltage Rating	120 VAC
Coil Power Rating DC	.085 W
Insulation Initial Dielectric Between Contacts & Coil	1000 Vrms

Body Features

Product Weight	40 g[1.41 oz]
Enclosure Type	Dust Protected



Contact Features

Contact Material	Ag
------------------	----

Termination Features

Main Termination & Connection Type	Solder/Plug-In Terminals
Coil Termination & Connection Type	Solder/Plug-In Terminals

Mechanical Attachment

Product Mounting Feature Type	Mounting Studs
Product Mount Type	Panel & Socket Mount

Dimensions

Product Width	18.66 mm[.734 in]
Product Length	24.13 mm[.95 in]
Product Height	29.97 mm[1.17 in]

Usage Conditions

Operating Temperature Range	-55 – 75 °C[-67 – 167 °F]
Environmental Category of Protection	RTI
Environmental Ambient Temperature (Max)	75 °C[167 °F]

Operation/Application

Current Type	DC
Coil Magnetic System	Monostable

Packaging Features

Packaging Method	Package
------------------	---------

Other

Coil Power Rating Class	0 – .1 W
Contact Current Class	16 A
Environmental Ambient Temperature Class	70 – 85 °C
Height Class (Mechanical)	30 – 40 mm
Length Class (Mechanical)	25 – 30 mm
Width Class (Mechanical)	16 – 20 mm

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------




EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.7% in 74019790) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1393143-2 27E129=SOCKET,R10,16,PC,PHEN	 TE Part # 2-1393143-5 27E213=SOCKET,R10,16,PC,PHEN	 TE Part # 4-1393143-4 27E461=SOCKET,R10,4POLE,PCB,TRCK-MNT,SCRW	 TE Part # 4-1393143-1 27E446=SOCKET,R10,2POLE,FLG-MNT,SOLDER
 TE Part # 5-1393143-1 27E637=SOCKET,R10,4POLE,PCB,.210	 TE Part # 1393143-9 27E126=SOCKET,R10,16,SLG,PHE	 TE Part # 2-1393143-2 27E194=SOCKET,R10,16,PC,PHEN	 TE Part # 4-1393143-8 27E629=SOCKET,R10,4POLE,PCB,.180







TE Part # 1-1393143-5
27E152=SOCKET,R10,ASSY,W/BRK

Also in the Series


Potter & Brumfield R10



Board-to-Board Headers & Receptacles(1)



PCB Headers & Receptacles(1)



PCB Relays(28)



Relay Accessories(27)

Customers Also Bought



TE Part #4-1393766-6
R10-E1Y4-JJ1.0K=R10




TE Part #696730-1
PIDG 16-14HD BUTT SPLICE




TE Part #4-1437664-9
NC6-P108-14=NC6 ASSEMBLY




TE Part #3-1879350-5
RR01 5% 5R6 AMMO



TE Part #69653
HYP8 AMPOWER 350MCM 69082 DIE SET



TE Part #53682-2
TERMINAL,AMPOWER 3/0 1/2



TE Part #1520238-1
8630K50=8 AMP ROCKER



TE Part #4-1393766-8
R10-E1Y4-J1.0K=R10



TE Part #1-1437507-5
8136-475G4=JUMPER PLUG ASSY



TE Part #328178
TERMINAL,AMPOWER 4 1/2



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1393766-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1393766-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1393766-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

R10 General Purpose Dry Circuit to 7.5 Amp Multicontact AC or DC Relay

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

CSA Certificate

English