

SPEED SLOT® CARBIDE
TIPPED HOLE SAWS

For Drilling Holes in Wood, Steel, Stainless
Steel, Cast Iron & Abrasive Materials



CARBIDE TIP

UP TO 50X LIFE*

UP TO 50X LIFE*

High performance carbides are welded to the cutting edge for durability and to help prevent tooth loss

EXTREMELY VERSATILE

Aggressive tooth design drills through wood, steel, stainless steel, cast iron, fiber cement and plaster

FAST, EASY PLUG REMOVAL

SPEED SLOT® staircase design has multiple leverage points for easy plug ejection

SPEED
SLOT®



*vs LENOX Bi-Metal Hole Saw cutting cast iron



APPLICATION

Nail-Embedded Wood	Steel	Stainless Steel
Drywall / Plaster	Cement Board	Cast Iron

** For additional information see page 4

SPEED SLOT® CARBIDE TIPPED HOLE SAWS

For Drilling Holes in Wood, Steel, Stainless Steel,
Cast Iron & Abrasive Materials

UP TO 50X LIFE*

High performance carbides are welded to the cutting edge for durability and to help prevent tooth loss

FAST, EASY PLUG REMOVAL

SPEED SLOT® staircase design has multiple leverage points for easy plug ejection

EXTREMELY VERSATILE

Aggressive tooth design drills through wood, steel, stainless steel, cast iron, fiber cement and plaster

*vs LENOX Bi-Metal Hole Saw cutting cast iron



1 PER PACK	DIAMETER		PIPE TAP		PIPE ENTRANCE		USE ARBOR			RECOMMENDED RPM				
PROD NO	IN	MM	IN	MM	IN	MM	SNAP-BACK™	STANDARD	ALUM	STAINLESS STEEL	FIBER-GLASS	CERAMIC TILE	CAST IRON	
LXAH31116	11/16	17.5	—	—	—	—	5L	1L, 4L, 5L	1800	690	270	550	240	
LXAH334	3/4	19.1	1/2	12.7	3/8	9.5	5L	1L, 4L, 5L	1700	640	250	500	210	
LXAH378	7/8	22.2	3/4	19.1	1/2	12.7	5L	1L, 4L, 5L	1500	550	210	430	180	
LXAH31	1	25.4	—	—	—	—	5L	1L, 4L, 5L	1300	480	190	370	150	
LXAH3118	1-1/8	28.6	1	25.4	3/4	19.1	5L	1L, 4L, 5L	1100	420	170	330	140	
LXAH3114	1-1/4	31.8	—	—	—	—	2L, 6L	2L, 3L, 6L	1000	380	160	300	130	
LXAH3138	1-3/8	34.9	—	—	1	25.4	2L, 6L	2L, 3L, 6L	900	350	140	270	110	
LXAH3112	1-1/2	38.1	1-1/4	31.8	—	—	2L, 6L	2L, 3L, 6L, 7L	900	320	120	250	100	
LXAH3158	1-5/8	41.3	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	700	290	110	230	90	
LXAH3134	1-3/4	44.5	1-1/2	38.1	1-1/4	31.8	2L, 6L	2L, 3L, 6L, 7L	700	270	110	210	90	
LXAH32	2	50.8	—	—	1-1/2	38.1	2L, 6L	2L, 3L, 6L, 7L	600	240	90	190	80	
LXAH3218	2-1/8	54.0	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	600	220	90	180	70	
LXAH3214	2-1/4	57.2	2	50.8	—	—	2L, 6L	2L, 3L, 6L, 7L	600	210	80	170	70	
LXAH3238	2-3/8	60.3	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	600	200	80	160	70	
LXAH3212	2-1/2	63.5	—	—	2	50.8	2L, 6L	2L, 3L, 6L, 7L	500	190	70	150	60	
LXAH32916	2-9/16	65.1	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	500	190	70	140	60	
LAH3258	2-5/8	66.7	2-1/2	63.5	—	—	2L, 6L	2L, 3L, 6L, 7L	500	180	70	130	60	
LXAH321116	2-11/16	68.3	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	500	180	60	120	60	
LXAH3	3	76.2	—	—	2-1/2	63.5	2L, 6L	2L, 3L, 6L, 7L	400	160	60	120	50	
LXAH3314	3-1/4	82.6	3	76.2	—	—	2L, 6L	2L, 3L, 6L, 7L	400	150	60	110	50	
LXAH3338	3-3/8	85.7	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	400	140	60	110	50	
LXAH3312	3-1/2	88.9	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	400	140	50	110	50	
LXAH3358	3-5/8	92.1	—	—	3	76.2	2L, 6L	2L, 3L, 6L, 7L	400	130	50	100	40	
LXAH3334	3-3/4	95.3	3-1/2	88.9	—	—	2L, 6L	2L, 3L, 6L, 7L	300	130	50	110	40	
LXAH34	4	101.6	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	300	120	50	100	40	
LXAH3418	4-1/8	104.8	—	—	3-1/2	88.9	2L, 6L	2L, 3L, 6L, 7L	300	120	50	90	40	
LXAH3414	4-1/4	108.0	4	101.6	—	—	2L, 6L	2L, 3L, 6L, 7L	300	110	50	90	40	
LXAH3412	4-1/2	114.3	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	300	110	40	80	30	
LXAH3434	4-3/4	120.7	4-1/2	114.3	4	101.6	2L, 6L	2L, 3L, 6L, 7L	300	100	40	80	30	
LXAH35	5	127.0	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	200	100	40	80	30	
LXAH3512	5-1/2	139.7	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	200	100	40	70	30	
LXAH36	6	152.4	—	—	—	—	2L, 6L	2L, 3L, 6L, 7L	100	80	30	60	30	

Note: We recommend the use of a carbide tipped pilot drill when cutting hard materials. Bits available in standard and long lengths—3 1/4" (83mm) LXAH9314CTPB and 4 1/4" (108mm) LXAH9414CTPB.

PLUMBER'S KIT

**LXAH3PSET6
8 PIECE**

19.1, 22.2, 28.6,
38.1, 44.5, 57.2mm
Arbors: 1L, 2L

MEDIUM KIT

ELECTRICIAN'S KIT

**LXAH3LSET6
8 PIECE**

22.2, 28.6, 34.9,
44.5, 50.8, 63.5mm
Arbors: 1L, 2L

MEDIUM KIT

CONTRACTOR'S KIT

**LXAH3GSET11
15 PIECE**

19.1, 22.2, 25.4, 28.6,
31.8, 34.9, 38.1, 44.5,
50.8, 65.1, 76.2mm
Arbors: 1L, 2L
Two pilot drills

LARGE KIT