



Main

Range of product	TeSys
Device short name	LE2D
Product or component type	Enclosed DOL starter
Motor starter type	Reversing
Motor power kW	4 kW at 380/400 V AC 50/60 Hz 4 kW at 415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 2.2 kW at 220/230 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz 5.5 kW at 660/690 V AC 50/60 Hz
Utilisation category	AC-3
[Uc] control circuit voltage	400 V AC 50/60 Hz
[Ith] conventional free air thermal current	9 A
Control type	1 2-position spring return selector switch I-II 1 red stop/reset button O red
Enclosure material	Polycarbonate

Complementary

Device composition	Contactors
Protection type	Thermal protection via thermal overload relay to be ordered separately
Cable entry	2 x 16 mm PG at bottom 2 x 20 mm ISO at top 2 x 20 mm PG at bottom 2 x 21 mm PG at bottom 2 x 25 mm ISO at top 2 x 25 mm PG at bottom
Width	101 mm
Height	201 mm
Depth	160 mm
Product weight	2.1 kg

Environment

IP degree of protection	IP657 conforming to IEC 60529
Standards	EN 60947 IEC 60439-1 IEC 60947-4-1 VDE 0660-102
Ambient air temperature for operation	-5...40 °C