

## Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and Silver

## RS PRO Fire Sleeve Blue 15M

RS Stock No.: 0761198



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

## General Specifications

Part Number	Ordering Size (mm)
0731207	4
0761185	6
0761186	8
0761188	10
0761189	12
0761190	14
0761191	16
0761192	19
0761131	22
0761132	25
0761133	28
0761134	32
0761135	35
0761136	38
0761138	41
0761139	44
0733658	51
07303805	57
0733661	63
0733662	70
0761194	76
0761195	83
0761196	89
0761197	95
0761198	102
0761199	114
0761201	127
0761202	140
0761203	152
0761204	168
0761205	180
0761206	203

## Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2