



PRODUCT-DETAILS

# OTE36TL3M

## OTE36TL3M EMC safety switch



### General Information

Extended Product Type	OTE36TL3M
Product ID	1SCA022614R0610
EAN	6417019200156
Catalog Description	OTE36TL3M EMC safety switch

Long Description	<p>EMC safety switch, 3-p. 415V AC23 45A, 22kW. Mounted auxiliary contact: 1NO0NC. Plastic enclosure. IP65. Black Selector handle. Interlocked cover. Defeatable interlocking. The enclosure in the OTE series is using a rigid glass reinforced polycarbonate enclosure. The enclosure is UV protected, protected against low-pressure water jets (IP65), and hence built for outdoor and indoor use. The cable entries are threaded and have knock out holes for 2 parallel cables and one control cable, both from top and bottom. The handle is padlockable and made for three padlocks. The handle is lockable in ON and OFF position. The interlocking can be bypassed, for thermographing etc. The switch is made for 5 wire system, and have a fixed neutral terminal and PE terminal. The EMC protection is utilized by a metal plate in the bottom, connected to the cable shield with clamps, included in the delivery. No EMC glands needed.</p>
------------------	--

### Material Compliance

Conflict Minerals Reporting Template	9AKK108467A5658
--------------------------------------	-----------------

(CMRT)

REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

## Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340003M0016 9AKK108466A4485
Mechanical Drawings	OTPK201490SM32.stp

## Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Last Ordering Date	2026-08-31 All Countries
Replacement Product ID (NEW)	No new type
Country or Territory of Origin	Finland

## Dimensions

Product Net Width	145 mm
Product Net Height	200 mm
Product Net Depth / Length	90 mm
Product Net Weight	0.9 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	162 mm
Package Level 1 Depth / Length	222 mm
Package Level 1 Height	148 mm
Package Level 1 Gross Weight	1 kg
Package Level 1 EAN	6417019200156

## Technical

Cable Cross-Section	1.5 ... 35 mm <sup>2</sup>
Cable Entry Position	Top and/or Bottom

Cable Outlets Per Side	2xM32+M16 / 2xM32+M16
Color	RAL7035
Connecting Capacity Main Circuit	Screw Clamp 1.5 ... 35 mm <sup>2</sup> Screw Clamp / PE Terminal 2pc,1.5 ... 35 mm <sup>2</sup>
Conventional Thermal Current (I <sub>the</sub> )	Fully Enclosed 80 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Plastic
Handle Color	Black
Handle Type	Selector handle
Impact Resistance Rating	Housing IK08
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC
Mounted Auxiliary Contacts	1 NO, 0 NC
Neutral Type	Fixed Neutral
Number of Auxiliary Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Poles	3P
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out
Position of Neutral Terminals	Top In - Bottom Out
Position of PE Terminals	Top In - Bottom Out
Power Loss	at Rated Operating Conditions per Pole 4.5 W
Rated Insulation Voltage (U <sub>i</sub> )	acc. to IEC/EN 60664-1 750 V
Rated Operational Current AC-22A (I <sub>e</sub> )	(380 ... 415 V) 63 A (500 V) 63 A (690 V) 63 A
Rated Operational Current AC-23A (I <sub>e</sub> )	(380 ... 415 V) 45 A (500 V) 45 A (690 V) 20 A
Rated Operational Power AC-23A (P <sub>e</sub> )	(380 ... 415 V) 22 kW (500 V) 22 kW (690 V) 15 kW
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity (I <sub>cm</sub> )	(690 V AC) 2.1 kA
Rated Short-time Withstand Current Low Voltage (I <sub>cw</sub> )	for 1 s 1.5 kA
Special Functions	EMC
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 2 N·m
Wire Stripping Length	13 mm

### Technical UL/CSA

Wire Stripping Length	13 mm
Tightening Torque	Main Circuit 2 N·m

---

### Certificates and Declarations

---

BV Certificate	1SCC340018D0204
Declaration of Conformity - CE	1SCC340004D2705
DNV GL Certificate	1SCC340045D0203

---

---

### External Classifications and Standards

---

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

---

### Categories

---

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

