

LIFTING TABLES



300 KG

Hand cranked, Single scissors

Lifting tables designed for occasional use to lift, transport and maintain loads at height.

- Height adjustable to the nearest millimetre by crank handle and worm screw column.
- Load kept level, even over long periods, without lowering the platform.
- No oil loss.
- Particularly robust, hard-wearing and maintenance-free.
- Epoxy paint.
- 2 fixed wheels + 2 polyurethane swivel wheels with brakes.
- Supplied with unmounted wheels, user manual and CE certificate in French.



855 007 769



Wheels 855 007 767

Reference	CU kg	Tray dimensions mm	Minimum/maximum height	Lifting stroke	Crank turns	Overall dimensions mm (WxDxH)	Wheel Ø mm	Weight kg
855 007 767	300	950 x 600	410 / 1025 mm	615 mm	75	1140 x 600 x 1025	125	65
855 007 769		1150 x 750	410 / 1050 mm	640 mm		1300 x 750 x 1050	125	77

