MSA
The Safety Company

Non-vented helmet - Fully featured for an unparalleled protection



V-Gard 500 non-vented Safety Helmet

Key features and benefits

- UV stabilised ABS helmet shell offers good resistance to scratches
- Provides lateral crush protection
- Built-in rain gutter for outdoor operations
- Standard slots to easily attach MSA visors and/or ear muffs
- 2-or-4 point chinstraps available, including V-Gard universal 4-point chinstrap, chincup in option
- 8 shell colours: white, yellow, red, blue, green, orange, grey and black
- Optional: badge holder for the front, branding; individual naming stickers; reflective stickers
- Lifetime: 3 years storage, +5 years service time; MSA delivers stickers to note date of first use and stick to inside shell
- Ideal electrician helmet meeting EN 397 440 V AC and EN 50365 1000 V AC
- Ideal design for adapting earmuffs, visors or attaching headband of MSA eyewear with goggle adapter

- Anti-static assembly; ELECTROSTATIC-INERIS certified for use in ATEX/ explosive environments
- 3 suspensions available:
- -Push-Key with slide adjustment and wipeable PVC sewn in sweatband
- -Fas-Trac® III with wheel ratchet and sweat-wicking foam sweatband
- -Fas-Trac® III with wheel ratchet and wipeable PVC sewn in sweatband

Non-vented helmet - Fully featured for an unparalleled protection



MSA Suspensions - General features and benefits

- · Overhead straps made of woven polyester providing high comfort and long term, consistent shock absorption performance
- Ensures consistent performance and comfort level even under the influence of moisture or low temperatures
- Sophisticated 4-point attachment: good positioning, stability and better air circulation
- · Ideal positioning of the harness through height and length adjustment: perfect for use with face masks
- Self-adjusting textile crown straps for fast height adjustment and comfortable fit





MSA Push-Key suspension

Features and benefits

• EASE OF USE:

- This is the fastest sliding suspension on the market: simple push to loosen, squeeze to tighten
- Can be adjusted with one hand even when worn

• SURE FITTING:

– It offers greater retention capacity than competitive sliding suspensions because it's so much easier to select the best adjustment position

ADJUSTABILITY:

- 2 levels of nape adjustment for fitting comfort
- Designed to avoid interference with other PPE such as ear muffs

• SWEATBAND COMFORT:

- Sewn in PVC perforated wipeable sweatband

MSA Fas-Trac® III suspension

Features and benefits

• BALANCE & STABILITY:

- Lower nape strap improves retention: Helmets stay on when leaning over
- Adjusts for a custom fit to the back of the head

HEADBAND COMFORT:

- The comfort pad by separating the ratchet from the head, cradles the head increasing comfort and cooling airflow
- Prevents hair from getting pulled

• EASE OF USE:

- Ratchet offers smooth rotation: reduced effort to turn
- Easy grip knob adjustable even with gloves on

• ADJUSTABILITY:

- Three levels of nape height adjustment giving superior nape fit
- Avoids interference with other PPE such as ear muffs

SWEATBAND COMFORT:

- Largest sweatband surface area on the market covers more of the headband and user's forehead for increased comfort
- 2 different sweatband options: sewn in PVC perforated wipeable or sweat-wicking washable foam(breathable fabric allows direct air permeation)
- Replaceable foam sweatband can be attached over the existing sweatband without demounting the suspension

Also available Terry cotton washable sweatband that can be used over both sewn in PVC or replaceable foam sweatbands for increased user comfort









Non-vented helmet - Fully featured for an unparalleled protection

Technical Specifications

Shell			
	ADC (Agrilanitile Distantiana Ct. wana) IIV stabilizad Nan Vantad		
Shell material	ABS (Acrylonitrile Butadiene Styrene), UV stabilized, Non-Vented		
Weight	270g		
Suspensions			
Weight	Push-Key with slide adjustment and wipeable PVC sewn in sweatband: 70 g		
	Fas-Trac® III with wheel ratchet and sweat-wicking foam sweatband: 89 g		
	Fas-Trac® III with wheel ratchet and wipeable PVC sewn in sweatband: 91 g		
Webbing	Black Polyester (PET), double straps, 4 points		
Sweatband material	Push-Key with wipeable sewn in PVC sweatband and Polyurethane (PU) internal foam.Nontoxic		
	PVC in contact with the head.		
	Fas-Trac® III with wipeable sewn in PVC sweatband and Polyurethane (PU) internal foam. Nontoxic		
	PVC in contact with the head.		
	Fas-Trac® III with sweat-wicking Polyurethane (PU) internal grey foam and grey Polyamide (PA) finish in		
	contact with the head. Machine or hand washing (max. 50 cycles)		
Headband	Fas-Trac® III: Polypropylene (PP)		
Clina	Push-Key: Low Density Polyethylene (LDPE)		
Clips	Grey Polypropylene (PP)		
Comfort pad (Fas-Trac® III)	Low Density Polyethylene (LDPE) The Type (LL) (Patch at), Palmay monthylene (POM), Palmay related (PD) and Palmay idea (PD).		
Adjustment	Fas-Trac® III: (Ratchet): Polyoxymethylene (POM), Polypropylene (PP) and Polyamide (PA) Push-Key: (Button): Polyoxymethylene (POM)		
Size Metal parts	No No		
Approvals Standard	Certified by European Notified Body DGUV (0299) according to: EN 397: 2012		
Mandatory Tests			
	Shock absorption, resistance to penetration, flame resistance, chinstrap anchorage		
Optional Tests	Very low temperature / -30°C, electrical insulation / 440 V AC, Lateral Deformation / LD		
Other standards	Certified by European notified body DGUV (0299) according to: EN 50365:2002 electrical class 0		
\wedge	nominal voltage up to 1000 V A.C. and 1500 V D.C. The voltage used for this test is 10 000 V.		
<u>∕</u> 1000 V	Certified by INERIS to EN ISO 80079-36 : 2016 & CEI/TS 60079-32 : 2017 for safe use in ATEX areas* (ELECTROSTATIC-INERIS Certificate n° 29406)		
	- Industry:		
ELECTROSTATIC	Dust: hazardous zones 20, 21, 22 (all zones)		
Ex	Gas: zones 1 and 2 with gas group IIA (propane)		
INERIS	- Mines: any type of extraction and any depth		
	*Caution: when working in an ATEX area operatives must be fully equipped with appropriate PPE eg.		
	dissipative shoes (earth resistance less than 1.108 Ω), not just suitable industrial helmets!		
Lifetime guidelines			
Storage time (when helmet not used)	3 years from shell injection date (helmet packed in proper condition, not exposed to light, chemical		
	or any type of pollution). Store in a proper storage bag and/or in a closed cabinet to avoid extended		
	exposure to sunlight, cold, humidity, exhaust fumes, etc. If the helmet has been stored more than 3		
	years, deduct the extra storage time from the recommended helmet's service life. NB: For EN 50365		
Consider life (in addition to the atomore time)	class 0 helmets recommended storage temperature 20 ±15 °C to ensure performance		
Service life (in addition to the storage time)	5 years from actual starting date of use. MSA recommends writing the date of first use onto a sticker (supplied with each helmet) and then sticking into the shell. This is normally the point at which		
	service life starts		
Suspension (Push-Key and Fas-Trac® III)	Replace when damaged or contaminated , or as required for hygienic reasons		
buspension (rush ney unu rus muc ill)	neplace when darraged or contaminated, or as required for hygicine reasons		



Non-vented helmet - Fully featured for an unparalleled protection

Packaging

	Description	
Individual (sales unit)	One helmet in a protective plastic bag with instructions, 1 tab suspensions fitted or	
	4 tabs suspensions fitted (GVxxx-xxAxxxx-xxx)	
Box	Minimum order quantity: 20 helmets	
	Box size: 706x586x455 mm (one tab fitted) or 720x610x460 mm (4 tab fitted)	
Pallet	200 helmets (10 boxes of 20 helmets) - Pallet size: 1200 x 730 x 1980 mm	

Ordering Information

Colors	RAL Code	V-Gard 500 NV PK PVC sweatband	V-Gard 500 NV FTIII PVC Sweatband	V-Gard 500 NV FTIII foam sweatband		
White	RAL 9003	GV511-0000500-000	GV512-0000500-000	GV519-0000500-000		
Yellow	RAL 1018	GV521-0000500-000	GV522-0000500-000	GV529-0000500-000		
Red	RAL 3020	GV531-0000500-000	GV532-0000500-000	GV539-0000500-000		
Green	RAL 6016	GV541-0000500-000	GV542-0000500-000	GV549-0000500-000		
Blue	RAL 5003	GV551-0000500-000	GV552-0000500-000	GV559-0000500-000		
Orange	RAL 2008	GV561-0000500-000	GV562-0000500-000	GV559-0000500-000		
Gray	RAL 7036	GV571-0000500-000	GV572-0000500-000	GV579-0000500-000		
Black	RAL 9004	GV581-0000500-000	GV582-0000500-000	GV589-0000500-000		
Part No.	Description	Description ATO digit when fitted to helmets				
10162752	Fas-Trac® III suspensi	Fas-Trac® III suspension with ratchet and sewn in PVC sweatband GVx.				
10162755	Fas-Trac® III suspensi	Fas-Trac® III suspension with ratchet and replaceable, washable, foam sweatband				
10162507	Push-Key suspension	Push-Key suspension with slide adjustment and sewn in PVC sweatband				
10153518	Fas-Trac® III foam sw	Fas-Trac® III foam sweatband (10 pcs) – replacements for 10162755 or GVxx9 or over				
696688	Terry cotton (Terri-Ba	Terry cotton (Terri-Band) sweatband (10 pcs) – for use over sewn in PVC sweatband				

Other accessories and options	Ask for our detailed data-sheets
Options	Lamp brackets
Options	Logo Customization
Accessories or Options	Chinstraps
Accessories or Options	High visibility stickers
Accessories	Helmet mounted ear-muffs
Accessories	Individual naming
Accessories	Frame and visors
Accessories	Winter liners
Accessories	Cooling liners
Accessories	Neck curtains
Accessories	Goggles Clips

