



Image may differ from product. See technical specification for details.



## LAGF 18

SKF Grease Filler Pump LAGF 18

Best lubrication practices say that each type of grease requires an individual grease gun and that the refilling has to be a clean process. SKF Grease Filler Pumps are designed to achieve this goal. The LAGF 18 is operated with a mechanical lever and enables optimum cleanliness for filling grease guns from a 18 kg drum.

- Quick filling with low pressure high stroke volume
- Easy usage with all items included
- Tested and approved for all SKF greases
- Ideal for usage together with SKF Bearing Packer VKN 550

# Overview

## Performance

Maximum pressure	30 bar
------------------	--------

## Properties

Recommended applications	grease filler pump for drums or pails designed to fill grease guns or TLRD grease dispensers
For type/size of grease drum	18 kg grease pails
Operation	manual pump with handle
Mobility	stationary
NLGI class of lubricant (max)	2
Connection	greasing point: DIN 1283 nipple
Maximum pressure	3 MPa
Suitable drum inner diameter	265.0 – 285.0 mm
Suitable drum inside height (max)	420 mm
Air pressure	[object Object] bar
Volume per stroke	45 ml
Hose	No
Optional Trolley	LAGT 18 - 50
Power source	manual
Material	steel
Material handle	steel with plastic grip
Ambient temperature range	10.0 – 40.0 °C
Recommended storage temperature	10.0 – 40.0 °C
Relative humidity	< 65 %
Content	grease pump with pump handle, drum cover plate, drum followerplate

## Logistics

Product net weight	4.12 kg
eClass code	23-06-91-06
UNSPSC code	15121902

## Compatible products

## Accessory

Grease trolley for 18 kg and 50 kg drums	<a href="#">LAGT 18-50</a>
Bearing packer	<a href="#">VKN 550</a>

## Recommended product

SKF Grease Gun TLGH 1	<a href="#">TLGH 1</a>
SKF Grease Gun 1077600	<a href="#">1077600</a>
SKF Grease Gun 1077600 H	<a href="#">1077600 H</a>
SKF Grease Gun 1077600/SET	<a href="#">1077600/SET</a>
SKF Grease Gun LAGH 400	<a href="#">LAGH 400</a>
SKF Battery Driven Grease Gun TLGB 20	<a href="#">TLGB 20</a>
Battery driven grease gun (110V charger)	<a href="#">TLGB 20/110V</a>
SKF Lincoln Battery Driven Grease Gun TLGB 1262-E	<a href="#">TLGB 1262-E</a>
SKF Lincoln Battery Driven Grease Gun TLGB 1886-E	<a href="#">TLGB 1886-E</a>

# Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

## Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

## Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

## Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

## Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

## Changes

SKF reserves the right to make changes or additions to this website / app at any time.