



Triple needle stitched structural seams have a Lifetime Seam Guarantee



Combat pockets with flaps for secure storage



External kneepad pockets to fit ProGARM™ 2240 Kneepad



7522

HI-VIS DUNGAREE

SIZES: 30"- 52" Reg leg (32"/81cm)
32"- 44" Tall leg (34"/86cm)
30"- 42" Short leg (30"/76cm)

PRODUCT INFORMATION

COLOUR: Navy/HV Yellow

FABRIC SPECIFICATION:
VXS+ 300W 300g/m2 Woven Inherent Fabric, VXS+ 300W 300g/m2 Woven Ripstop Fabric

PRODUCT CARE:



- ✓ Cordura® knee & hem reinforcement // Up to 200,000 abrasion cycles
- ✓ 5cm and 7cm FR AS industrial wash reflective tape // Stitched on for durability
- ✓ External kneepad pockets // For extra comfort and knee protection
- ✓ Open tool/pen pocket on leg // Easy access to tools
- ✓ Combat pocket with flap // Safe storage space for phone
- ✓ Two rear pockets with flaps // Secure storage space
- ✓ Side access pockets // For easy access storage
- ✓ Large chest pocket with flap // Safely stores mobile phone
- ✓ Extra wide belt loop at rear // Prevents belt riding up
- ✓ Adjustable braces attached to bib rear // Provides comfort-fit
- ✓ ThermSAFE™ plastic FR zipper and brace buttons // CE Certified
- ✓ SafetyICON™ on leg pocket // Visual EN Norm icon system
- ✓ Triple stitched structural seams // Lifetime quality

EN STANDARDS

EN ISO 11612: 2015	EN 1149-5: 2018	EN 61482-2: 2020	EN ISO 20471: 2013 +A1:2016
A1, B1, C1, F1	Pt. 5:2018 Pt. 3:2004 Charge Decay	APC1 ELIM=9cal/cm² ATPV=12.9cal/cm²	Class 1

BOX TEST



ARC RATING



FABRIC

