



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Male Screwlock**

Primary Product Material: **Stainless Steel, Zinc Alloy**

Operating Temperature (Max): **150 °C [302 °F]**

Operating Temperature Range: **-55 – 150 °C [-67 – 302 °F]**

Hardware Accessory Function: **Latching, Locking & Retention**

Features

Product Type Features

Connector Hardware Accessory Type	Male Screwlock
Hardware Accessory Function	Latching, Locking & Retention

Body Features

Primary Product Material	Stainless Steel, Zinc Alloy
--------------------------	-----------------------------

Mechanical Attachment

Hardware Type Included	Jackscrew Tip Male, Spirol Pin and Washer
Thread Size	6-32
Product Plating Finish	Trivalent Chromate

Dimensions

Product Width	4.75 mm[.187 in]
Product Length	34.65 mm[1.364 in]
Product Height	4.75 mm[.187 in]

Usage Conditions

Operating Temperature (Max)	150 °C[302 °F]
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]



Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(5)




Connector Caps & Covers(14)



Connector Hardware(46)



Connector Strain Relief(13)




PCB Headers & Receptacles(9)



Rack & Panel Connectors(1)



Rectangular Power Connectors(82)




Wire-to-Board Headers & Receptacles (1)


Customers Also Bought



TE Part #322338
DIAMOND GRIP 16-14 HT R 10



TE Part #936969-000
202K132-4/86-0



TE Part #48132
HYP8 SOLIS 1/0AWG NEST



TE Part #608036-1
SILICONE FUSION TAPE,1"X36'



TE Part #ZPF000000000008922
983-6SE 18-14 SN-L



TE Part #321017
TERMINAL,PIDG R 26-22 4



TE Part #48133
HYP8 SOLIS 2/0AWG NEST



TE Part #6-1437558-9
MTE106E=(MSTE) SW TOG WATERPRO



TE Part #48131
HYP8 SOLIS 1/0-4/0AWG INDENTER

TE Part #CA7155-000
HT-SCE-1K-1-1/2-2-0-6



Documents

Product Drawings

MALE JACKSCREW ASSM.

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_203535-2_F.3d_igs.zip

English

Customer View Model

ENG_CVM_203535-2_F.3d_stp.zip

English

Customer View Model

ENG_CVM_203535-2_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_203535-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_203535-2_D.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_203535-2_D.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

English

FLEXIBLE FLAT CABLE (FFC) JACKSCREW ASSEMBLIES AND LATCH-TYPE HAR

English