

# WT-HF 4,5X430 - Cable tie



3240770

<https://www.phoenixcontact.com/gb/products/3240770>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, standard version

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3240770             |
| Packing unit                         | 100 pc              |
| Minimum order quantity               | 100 pc              |
| Sales key                            | BE7131              |
| Product key                          | BE7131              |
| Catalog page                         | Page 614 (C-3-2019) |
| GTIN                                 | 4046356704885       |
| Weight per piece (including packing) | 2.96 g              |
| Weight per piece (excluding packing) | 2.94 g              |
| Customs tariff number                | 39269097            |
| Country of origin                    | IT                  |

# WT-HF 4,5X430 - Cable tie

3240770

<https://www.phoenixcontact.com/gb/products/3240770>



## Technical data

### Product properties

|                      |                |
|----------------------|----------------|
| Product type         | Cable tie      |
| Type                 | Internal teeth |
| Tensile strength GRP | 220 N          |

### Dimensions

|        |        |
|--------|--------|
| Width  | 4.8 mm |
| Length | 430 mm |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | transparent                    |
| Material                               | PA 6.6                         |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Cable/line

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 3.5 mm ... 115 mm |
| Tensile strength        | 220 N             |

### Environmental and real-life conditions

#### Ambient conditions

|                                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Optimum ambient temperature (storage/transport) | 23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Ambient temperature (operation)                 | -40 °C ... 85 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Ambient temperature (assembly)                  | -10 °C ... 60 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Resistance to UV radiation                      | no                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Short-term temperature                          | 110 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

# WT-HF 4,5X430 - Cable tie

3240770

<https://www.phoenixcontact.com/gb/products/3240770>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240770>

### DNV

Approval ID: TAE00004VK



### UL Recognized

Approval ID: E328576-20210901

# WT-HF 4,5X430 - Cable tie

3240770

<https://www.phoenixcontact.com/gb/products/3240770>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140702 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000046 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# WT-HF 4,5X430 - Cable tie

3240770

<https://www.phoenixcontact.com/gb/products/3240770>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)