
























# SERIES 1881 - SINGLE-POLE ROUND ROCKER SWITCHES

TO 12 (4) A 250 V AC

 single-pole	Actuator color / printing	Housing color	Terminal type								Terminal description	Contact distance in mm	Contact material	Actuator	EN 60335 cap. 30 conform "G"	Miscellaneous	Stock version	
			12 (4) A 250 V AC 1E4	10 (4) A 250 V AC 1E4	8 (8) A 250 V AC 5E4	6 (4) A 250 V AV 5E4	15 A 250 V AC 1 1/2 HP	15 A 125 V AC 3/4 HP	10 A 250 V AC 1/2 HP	10 A 125 V AC 1/3 HP								
<b>ON / OFF switch (SPST)</b>																		
1881.1103		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40			●
1881.1104		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40			●
1881.1105		White	●	●	●	●						4.8	≥ 3	Ag	IP 40			
1881.1106		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40	●		
1881.1108		Black	●	●	●	●						4.8	≥ 3	Ag	IP 51	●	with switching system cover	
1881.1109		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40			
1881.1111		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40			
1881.1112		White	●	●	●	●						1 mm longer 4.8	≥ 3	Ag	IP 51	●	with switching system cover	
<b>Normally open contact (SPNO)</b>																		
1881.1209		Black	●	●	●	●						4.8	≥ 3	Ag	IP 51		with switching system cover opening terminal 1b closed	
<b>Changeover switch (SPDT)</b>																		
1883.1105		Black	●	●			●	●				4.8	≥ 3	Ag	IP 40			
1883.1106		Black	●	●			●	●				4.8	≥ 3	Ag	IP 40	●		

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

FACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS