

Electrical data

Total power consumption (W)	43
Primary Supply/Product voltage - min (V)	220
Primary Supply/Product voltage - max (V)	240
Lamp power factor	0.9
THD (at 230 V, 50 Hz, full load, at 100% dimming level) ≤ xx.x %	20
Electrical protection	Class I
Control gear type	Not required
Dimmable	No
Dimming method	N/A
Drive current (mA)	175
Inrush Current (A)	2
Inrush Duration (µs)	100
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz
Max. products per 16A C Breaker	48
Max. products per 16A B Breaker	28
Connectable conductor cross section - Min (mm²)	1
Connectable conductor cross section - Max (mm²)	1

Lifetime data

Lifespan L70 B50	30000
Lifespan L80 B10	20000

Physical data

Housing colour	Black
IP rating	IP65
IK rating	IK05
Diffuser finish	Transparent
Diffuser material	Glass
Reflector finish	Not Applicable
Nominal Product Length (mm)	201
Nominal Product Width (mm)	156
Nominal Product Height (mm)	57
Weight (kg)	0.575

Packaging

Product EAN number	5410288901695
Packaging single length / height (cm)	16.1
Packaging single width (cm)	5.9
Packaging single depth (cm)	21.0
DUN14 (inner)	15410288901692
Units per outer package	6
Packaging outer length / height (cm)	38.2
Packaging outer width (cm)	17.4
Packaging outer depth (cm)	22.8

Safety data

Glow Wire Test (°C)	650
Optimal operating condition (°C)	-20-40