

servo motor BMH, Lexium 32, 3.3Nm, 6000rpm, keyed shaft, with brake, IP54, 16 multiturn encoder

BMH1001P17F2A

Product availability: Stock - Normally stocked in distribution facility

## Main

Device short name	ВМН				
Product or Component Type	Servo motor				
Maximum mechanical speed	6000 rpm				
Continuous stall torque	29.2 lbf.in (3.3 N.m) LXM32.D12N4 3 A, 400 V, three phase 29.2 lbf.in (3.3 N.m) LXM32.D12N4 3 A, 480 V, three phase 30.09 lbf.in (3.4 N.m) LXM32.D18N4 6 A, 400 V, three phase 30.09 lbf.in (3.4 N.m) LXM32.D18N4 6 A, 480 V, three phase				
Peak stall torque	95.6 lbf.in (10.8 N.m) LXM32.D12N4 3 A, 400 V, three phase 95.6 lbf.in (10.8 N.m) LXM32.D12N4 3 A, 480 V, three phase 95.6 lbf.in (10.8 N.m) LXM32.D18N4 6 A, 400 V, three phase 95.6 lbf.in (10.8 N.m) LXM32.D18N4 6 A, 480 V, three phase				
Nominal output power	800 W LXM32.D12N4 3 A, 400 V, three phase 800 W LXM32.D12N4 3 A, 480 V, three phase 1300 W LXM32.D18N4 6 A, 400 V, three phase 1300 W LXM32.D18N4 6 A, 480 V, three phase				
Nominal torque	16.8 lbf.in (1.9 N.m) LXM32.D12N4 3 A, 400 V, three phase 16.8 lbf.in (1.9 N.m) LXM32.D12N4 3 A, 480 V, three phase 27.4 lbf.in (3.1 N.m) LXM32.D18N4 6 A, 400 V, three phase 27.4 lbf.in (3.1 N.m) LXM32.D18N4 6 A, 480 V, three phase				
Nominal speed	4000 rpm LXM32.D12N4 3 A, 400 V, three phase 4000 rpm LXM32.D12N4 3 A, 480 V, three phase 4000 rpm LXM32.D18N4 6 A, 400 V, three phase 4000 rpm LXM32.D18N4 6 A, 480 V, three phase				
Product compatibility	LXM32.D12N4 400480 V three phase LXM32.D18N4 400480 V three phase				
Shaft end	Keyed				
IP Degree of Protection	IP54 standard				
Speed feedback resolution	32768 points/turn x 4096 turns				
Holding brake	With				
Mounting Support	International standard flange				
Electrical Connection	Rotatable right-angled connectors				

## Complementary

Range Compatibility	Lexium 32
[Us] rated supply voltage	480 V
Phase	Three phase
Continuous stall current	3.15 A
Continuous power	1.76 W

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum current Irms	11.2 A LXM32.D12N4 11.9 A LXM32.D18N4				
Maximum permanent current	11.93 A				
Second shaft	Without second shaft end				
Shaft diameter	0.7 in (19 mm)				
Shaft length	1.6 in (40 mm)				
key width	1.2 in (30 mm)				
Feedback type	Multiturn SinCos Hiperface				
Holding torque	48.7 lbf.in (5.5 N.m) holding brake				
Motor flange size	3.9 in (100 mm)				
Number of motor stacks	1				
Torque constant	1.08 N.m/A 248 °F (120 °C)				
Back emf constant	70.3 V/krpm 248 °F (120 °C)				
Number of motor poles	5.0				
Rotor inertia	3.68 kg.cm²				
Stator resistance	3.1 Ohm 68 °F (20 °C)				
Stator inductance	7.45 mH 68 °F (20 °C)				
Stator electrical time constant	4.5 ms 68 °F (20 °C)				
Maximum radial force Fr	900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm				
Maximum axial force Fa	0.2 x Fr				
Brake pull-in power	12 W				
type of cooling	Natural convection				
Length	6.7 in (170.3 mm)				
Centring collar diameter	3.7 in (95 mm)				
centring collar depth	0.1 in (3.5 mm)				
Number of mounting holes	4				
Mounting holes diameter	0.4 in (9 mm)				
Circle diameter of the mounting holes	4.5 in (115 mm)				
Net Weight	10.6 lb(US) (4.8 kg)				
Sizing reference	BMH1001P				
Network number of phases	3				
Accuracy error [angular]	4.8 °				
Temperature copper hot	275 °F (135 °C)				
Temperature magnet hot	212 °F (100 °C)				
Temperature magnet rt	68 °F (20 °C)				

# Ordering and shipping details

Category	US1PC5318282		
Discount Schedule	PC53		

GTIN	3606485195841		
Returnability	Yes		
Country of origin	DF		

# **Packing Units**

Unit Type of Package 1	PCE		
Nbr. of units in pkg.	1		
Package 1 Height	8.66 in (22.0 cm)		
Package 1 Width	7.87 in (20.0 cm)		
Package 1 Length	15.75 in (40.0 cm)		
Package weight(Lbs)	11.2 lb(US) (5.1 kg)		
Unit Type of Package 2	P06		
Number of Units in Package 2	24		
Package 2 Height	41.34 in (105.0 cm)		
Package 2 Width	31.50 in (80.000 cm)		
Package 2 Length	23.62 in (60.000 cm)		
Package 2 Weight	79.6 lb(US) (36.1 kg)		

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1446
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	A7df881f-135f-4256-b8c2-ea55d4c9a151
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

#### **Use Again**


○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

### BMH1001P17F2A

#### **Dimensions Drawings**

#### **Servo Motors Dimensions**

#### **Example with Straight Connectors**



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

#### Dimensions in mm

Straight connectors		Rotatable angled connectors		a (without broke)	(دراده المانين)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	128	170

#### Dimensions in in.


Zimonolono in ini						
Straight connectors		Rotatable angled connectors		c (without brake)	a (with brake)	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	5.03	6.69	

#### Performance Curves

## 400 V 3-Phase Supply Voltage


#### **Torque/Speed Curves**

Servo motor with LXM32•D12N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

## Servo motor with LXM32•D18N4 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 480 V 3-Phase Supply Voltage


### **Torque/Speed Curves**

Servo motor with LXM32•D12N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### Servo motor with LXM32•D18N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque