



Technical data

4T-14124/14276

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage

KIT CONTENT

4T-14276, 4T-14124

VISUAL (S)



4T-14124/14276
Single row tapered roller bearings



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	31,75 mm
D - External diameter	69,012 mm
B - Bearing/Inner ring width	19,583 mm
C - Outer ring width	15,875 mm
T - Total width	19,845 mm
d1 - External diameter inner ring	51 mm
a - Charge load application point	15,745 mm
Mass	0,36 kg

PRODUCT PERFORMANCE	
C - Dynamic load	53,5 kN
C0 - Static load	58 kN
Cu - Fatigue limit load	7,1 kN

PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.38
Y0 - Static axial load coefficient	0.86
Y2 - Upper axial load coefficient	1.57
N lim - Oil lubrication limit speed	7400 tr/min
N lim - Grease lubrication limit speed	5600 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	37,5 mm
db min - Min IR shoulder diameter	38,5 mm
Da max - Max shoulder diameter OR	60 mm
Db min - Min OR shoulder diameter	63 mm
ra max - Max fillet radius	0,8 mm
r1a - Max fillet radius	1,3 mm

KIT COMPONENT

Cone designation	4T-14124
Cup designation	4T-14276

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-14124/14276
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material

Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X_o	Y_o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table

