

# 3210 A-2ZTN9/MT33



## Double row angular contact ball bearing with seals on both sides

Double row angular contact ball bearings, with seals on both sides, correspond to a pair of single row angular contact ball bearings in a back-to-back arrangement, while requiring less axial space. Depending on the sealing execution, they can operate at high speeds and are more suitable than deep groove ball bearings for supporting large axial forces in both directions.

- High-speed capability
- Accommodate relatively high radial loads, high axial loads in both directions and tilting moments
- Suitable where a stiff bearing arrangement is required
- Require less axial space than equivalent pair of single row angular contact ball bearings
- Integral sealing prolongs bearing service life

## Overview

### Dimensions

Bore diameter	50 mm
Contact angle	30 °
Outside diameter	90 mm
Width	30.2 mm

### Performance

Basic dynamic load rating	51 kN
Basic static load rating	42.5 kN
Limiting speed	7 000 r/min
Reference speed	8 000 r/min
SKF performance class	SKF Explorer

### Properties


Arrangement of contact angle (double-row bearing)	Back-to-back (0)
Axial internal clearance	CN
Cage	Non-metallic
Coating	Without
Contact type	Normal contact (two-point contact)
Locating feature, bearing outer ring	None
Lubricant	Grease
Matched arrangement	No
Material, bearing	Bearing steel

Number of rows	2
Relubrication feature	Without
Ring type	One-piece inner and outer rings
Sealing	Shield on both sides
Sealing type	Non-contact
Universal matching bearing	No

# Technical Specification


SKF performance class

SKF Explorer



## Dimensions

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	30.2 mm	Width
d <sub>2</sub>	≈ 57.8 mm	Recess diameter inner ring shoulder
D <sub>2</sub>	≈ 82.1 mm	Recess diameter outer ring shoulder
r <sub>1,2</sub>	min. 1.1 mm	Chamfer dimension inner ring
a	52 mm	Distance pressure point(s)



## Abutment dimensions

d <sub>a</sub>	min. 57 mm	Abutment diameter shaft
d <sub>a</sub>	max. 57.5 mm	Abutment diameter shaft
D <sub>a</sub>	max. 83 mm	Abutment diameter housing
r <sub>a</sub>	max. 1 mm	Fillet radius

## Calculation data

Basic dynamic load rating	C	51 kN
Basic static load rating	C <sub>0</sub>	42.5 kN
Fatigue load limit	P <sub>u</sub>	1.8 kN
Reference speed		8 000 r/min

Limiting speed		7 000 r/min
Calculation factor	$k_r$	0.06
Calculation factor	$e$	0.8
Calculation factor	$X$	0.63
Calculation factor	$Y_0$	0.66
Calculation factor	$Y_1$	0.78
Calculation factor	$Y_2$	1.24

## Mass

Mass bearing		0.65 kg
--------------	--	---------

# Terms and conditions

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

## Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app. Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service. Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

## Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

## Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

## Changes

SKF reserves the right to make changes or additions to this website / app at any time.