






ENGLISH

## Datasheet

**RS PRO** Mobile Crimp Tool and Dies Kit for crimping electrical terminals.

Stock No: 485-925



## Features & Benefits:

- Crimp dies are kept together with a special pin to simplify handling.
- Reliable – crimping performance is consistent and accurate with a parallel action stroke.
- Easy to use – designed to give the user full visibility of the crimping process. Handles are shaped for low effort crimping with a one or two hand grip.
- Versatile – an easy-access release function allows fast and simple exchange of crimp dies. No special tools needed.
- Weight and size of the tool are optimized to make it easy to carry. Dies are kept in pairs and delivered in a modular reusable box.
- Hole in handle allows attachment of safety strap

## TECHNICAL DATA

Die set 492-9618 for crimping insulated terminals 0.1 - 0.4 & 4 - 6 mm<sup>2</sup>  
Die set 492-9624 for crimping insulated terminals 0.5 - 1.5 & 1.5 - 2.5 mm<sup>2</sup>  
Die set 492-9652 for crimping wire ferrules 0.25 - 10 mm<sup>2</sup>  
Die set 492-9630 for crimping non-insulated terminals 0.75 - 2.5 mm<sup>2</sup>  
Die set 492-9646 for crimping non-insulated terminals 4 - 10 mm<sup>2</sup>

### Tool Frame

Length: 234 mm/9.21"

Width: 31 mm/1.22"

Height: 64 mm/2.52"

Weight: 460 gr/1.23 lb

Description: Tool frame for mobile die sets.

Life span, cycles: 20,000

