

AI-GB 1,5-8 RD - Ferrule



2100069

<https://www.phoenixcontact.com/gb/products/2100069>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: red

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2100069 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BH341S |
| Product key | BH341S |
| GTIN | 4067923214132 |
| Weight per piece (including packing) | 0.12 g |
| Weight per piece (excluding packing) | 0.12 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

AI-GB 1,5-8 RD - Ferrule



2100069

<https://www.phoenixcontact.com/gb/products/2100069>

Technical data

Product properties


| | |
|--------------------|---|
| Product type | Cable end sleeve |
| Conductor category | stranded conductors, class 2, 5, 6 / B, C, K, M |
| Product property | Suitable for AWG/multi-standard cables due to the increased diameter of the insulating collar |
| | UL certified |
| | Made from soft tin-plated electrolytic copper |
| | Correspond to the requirements of UL 486F |
| | Plastic collar made of polypropylene |
| | Halogen-free |
| | Long/short-term temperature: +105°C/+120°C |

Connection data

Conductor connection

| | |
|---------------------------------------|---------------------|
| Conductor cross section flexible max. | 1.5 mm ² |
| Conductor cross section AWG max. | 16 |
| Stripping length | 11 mm |

Dimensions

| | |
|---|--|
| Dimensional drawing |  |
| Sleeve length | 14 mm |
| Length contact range | 8 mm |
| Maximum stripping length | 11 mm |
| Ferrule diameter | 1.8 mm |
| Sleeve wall thickness | 0.15 mm |
| Insulating collar thickness | 0.3 mm |
| Inner dimensions of the insulating collar | 3.7 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | red (RAL 3001) |
| Material | CU-DHP |
| Flammability rating according to UL 94 | HB |
| Coating | galvanically tin-plated |
| Surface characteristics | Tin-plated |
| Components | free from silicone and halogen |

Mechanical properties

AI-GB 1,5-8 RD - Ferrule



2100069

<https://www.phoenixcontact.com/gb/products/2100069>

Technical data

| | |
|---------------|-------|
| Sleeve length | 14 mm |
|---------------|-------|

Standards and regulations

| | |
|------------------------------|--|
| Design according to standard | Color code in accordance with DIN 46228-4, UL 486F-E |
|------------------------------|--|

Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI-GB 1,5-8 RD - Ferrule

2100069

<https://www.phoenixcontact.com/gb/products/2100069>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2100069>



cULus Listed

Approval ID: E488001

AI-GB 1,5-8 RD - Ferrule



2100069

<https://www.phoenixcontact.com/gb/products/2100069>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400201 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000005 |
|----------|----------|

AI-GB 1,5-8 RD - Ferrule



2100069

<https://www.phoenixcontact.com/gb/products/2100069>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk