

Features

- Electronically commutated DC motor
- With polarity reversal and blocking protection
- High output, quiet running
- Connecting wires 300 mm AWG 26
- Speed control
- Signal output

Specification

Rated Voltage	24 VDC
Operating Voltage	14 ... 26.4 V
Rated Speed	5000 rpm
Rated Current	70 mA
Rated Power	1.68 W
Max. Airflow	7.4 CFM, 12.6 m ³ /h
Max. Air Pressure	4.83 mm-H ₂ O
Noise	21 dBA (25 dBA max.)
Wire	2 Leads - 300 mm
Dielectric Strength	5 mA max @ 500 VAC 60 Hz 1 min.
Service Life	30000 hours @ 40 °C
Insulation Resistance	10 MOhm min. @ 500 VDC



Mechanical

Fan Size (See Dimension Drawing in Page 2)	40 x 40 x 20 mm
Frame	Thermoplastic Black / PBT 15% gf of UL94-V0
Fan Blade	Thermoplastic Black / PBT 15% gf of UL94-V0
Bearing	Sleeve Bearing
Weight	27 g


Environment

Ambient Operating Temperature	-10 ... 70 °C
Storage Temperature	-40 ... 75 °C
Operation Humidity	5 ... 90 % RH
Storage Humidity	5 ... 95 % RH


DC Axial Fan



Drawing



P-Q Curve



Art Nr.

RND 460-00071