




Relay Key Data

- PCB relay with forcibly guided contacts
- Protective separation between control and load circuit (leakage and creepage distances >8 mm)
- IEC 61810-3 type A
- Double and reinforced insulation between the contacts
- Contact mounting SIS422 4 NO / 2 NC
- Small external dimensions
- Nominal coil power approx. 0,66 W
- Holding coil power 0,20 W
- Coils for railway applications according to EN 50 155 on request

Dimensions



Contact Data

Contact material	AgCuNi + 0,2 µm Au
Type of contact	Single contact with notched crown
Rated switching capacity	250 VAC 6 A AC1 1500 VA
Electr. Life AC1 (360 S / h)	>90000
Inrush current max.	30 A for 20 ms
Switching voltage range	5 to 250 VDC / VAC
Switching current range*	3 mA to 6 A
Switching capacity range*	40 mW to 1500 W(VA)
Contact resistance (as delivered)	≤100 mΩ / 6 V / 100 mA


*Guided values

Standard coils for direct current

(other voltages on request)

Nominal voltage VDC	Min. pick-up voltage at 20 °C	Drop-out voltage at 20 °C	Nominal current in mA	Resistance in Ohm at 20 °C
5	3,5	≥0,5	133,0	37,5 ± 10%
9	6,3	≥0,9	73,7	122,0 ± 10%
12	8,4	≥1,2	55,8	215,0 ± 10%
18	12,6	≥1,8	37,1	485,0 ± 10%
24	16,8	≥2,4	29,7	860,0 ± 10%
48	33,6	≥4,8	13,9	3450,0 ± 10%
60	42,0	≥6,0	11,1	5400,0 ± 13%
110	77,0	≥11,0	6,0	18300,0 ± 15%

Circuit Diagram (relay top view)



Insulation Data

- Basic insulation	at 250 VAC
- Air and creepage distance	>4 mm
- Test voltage	2500 V / 50 Hz / 1 min
- Double or reinforced insulation	
- Air and creepage distance	at 250 VAC >5,5 mm
- Test voltage	4000 V / 50 Hz / 1 min
- Double or reinforced insulation	
- Air and creepage distance	at 250 VAC >8 mm
- Test voltage	4000 V / 50 Hz / 1 min
Test voltage contact open	1500 V / 50 Hz / 1 min
Creepage resistance	CTI 175
Pollution degree	2
Overvoltage category	III
Insulation resistance at Up 500 VDC	>100 MΩ

Additional Data

Mechanical endurance	>10 x 10 ⁶ operations
Switching frequency, mechanical	15 Hz
Response time (all NO closed)	typically 15 ms
Drop-out time** (NC closed)	typically 5 ms
Bounce time of NO contact	typically 2 ms
Bounce time of NC contact	typically 15 ms
Shock resistance 16 ms	NO > 10g NC > 9g
Vibration resistance (10-200 Hz)	NO > 10g NC > 3g
Resistance to short circuiting contacts	1000 A SCPD 6 A.gG / gL (pre-fuse)
Ambient temperature	-40°C to +85°C
Thermal Resistance	45 K / W
Temperature limit for coil	120°C
Weight	approx. 35 g
Mounting position	any
Type of protection	RT III
Solder bath temperature	270°C / 5 s

**without spark suppression

Tests, Regulations, Standards

Approvals




UL File E188953	Sec. 5
Insulation class IEC 60664-1	250 VAC
Fire protection requirements	UL 94 / V0
Standards	IEC 61810-1, IEC 61810-3


Options, Accessories

none available

Product Key



Contact Lifetime for NO Contacts




Maximal switching characteristics (DIN EN 60947-5-1)

AC 1:	250 V / 6 A
AC 15:	230 V / 3 A
DC 1:	24 V / 6 A
DC 13:	24 V / 5 A / 0,1 Hz
UL 508:	B300 / R300

Maximal contact load at AC 1 with 230 V:


- 2 contacts with 6 A each
- 3 contacts with 4 A each
- 4 contacts with 3 A each

Load Limit Curve with Direct Current



- 1) Inductive load L/R 40 ms
- 2) Resistive load

Excitation Voltage Range



- 1) Max. excitation voltage with contact load: ≤4 A
- 2) Min. excitation voltage (guaranteed values) without previous operation

Single relay on print, no heat accumulation due to surrounding components with self-heating, duty cycle 100%.