



SAFETY DATA SHEET FLEXANE PRIMER FL-10

RS REACH MSDS Date 01/11/07

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/UNDERTAKING

PRODUCT NAME FLEXANE PRIMER FL-10
 PRODUCT NO. 15980 DE
 SUPPLIER ITW DEVCON INDUSTRIAL
 PRODUCTS GmbH / KORROFLEX
 LIEBIGSTR.21
 D-24145 KIEL
 GERMANY
 T: 0049 (0) 431 718 83 0
 F: 0049 (0) 431 718 83 25
 itwdevcon@t-online.de

Supplied by:
RS Components Ltd.
 Birchington Road, Corby, Northants, NN17 9RS.
 Tel: +44 (0) 1536 402888 (8am to 8pm)
 Email: technical.help@rs-components.com

2 HAZARDS IDENTIFICATION

Harmful by inhalation, in contact with skin and if swallowed. Highly flammable. Irritating to eyes, respiratory system and skin.

CLASSIFICATION Xn;R20/21/22. Xi;R36/37/38. F;R11.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
ETHANOL	200-578-6	64-17-5	1-10%	F;R11
ISOBUTYL METHYL KETONE	203-550-1	108-10-1	10-30%	F;R11 Xn;R20 Xi;R36/37 R66
PHENOL	203-632-7	108-95-2	1-5%	Muta. Cat. 3;R68 T;R23/24/25 C;R34 Xn;R48/20/21/22
PROPAN-2-OL	200-661-7	67-63-0	10-30%	F;R11 Xi;R36 R67
TOLUENE	203-625-9	108-88-3	10-30%	F;R11 Repr. Cat. 3;R63 Xn;R48/20,R65 Xi;R38 R67

The Full Text for all R-Phrases are Displayed in Section 16

4 FIRST-AID MEASURES

GENERAL INFORMATION

Avoid contact with skin and eyes. Do not breathe vapour/spray. Show this safety data sheet to the doctor in attendance

INHALATION

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Contact physician if discomfort continues.

INGESTION

Do not induce vomiting. If vomiting occurs, the head should be kept low so that stomach vomit doesn't enter the lungs. Get medical attention immediately!

SKIN CONTACT

Remove affected person from source of contamination. Wash skin thoroughly with soap and water for several minutes. Contact physician if irritation persists.

EYE CONTACT

Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention. Contact physician if irritation persists.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Fire can be extinguished using: Alcohol resistant foam. Carbon dioxide (CO2). Dry chemicals.

FLEXANE PRIMER FL-10

SPECIAL FIRE FIGHTING PROCEDURES

Keep up-wind to avoid fumes. Avoid water in straight hose stream; will scatter and spread fire. Cool containers exposed to flames with water until well after the fire is out. Keep run-off water out of sewers and water sources. Dike for water control.

SPECIFIC HAZARDS

Highly flammable. Avoid breathing fire vapours. May travel considerable distance to source of ignition and flash back.

PROTECTIVE MEASURES IN FIRE

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

6 ACCIDENTAL RELEASE MEASURES

PERSONAL PRECAUTIONS

Warn everybody of potential hazards and evacuate if necessary. Remove sources of ignition. Avoid inhalation of spray mist and contact with skin and eyes. Wear protective clothing as described in Section 8 of this safety data sheet. Provide adequate ventilation.

ENVIRONMENTAL PRECAUTIONS

Do not allow to enter drains, sewers or watercourses. Spillages or uncontrolled discharges into watercourses must be IMMEDIATELY alerted to the Environmental Agency or other appropriate regulatory body.

SPILL CLEAN UP METHODS

Absorb with sand or other inert absorbent. Transfer to a container for disposal. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined workplace exposure limit is not exceeded. Take precautionary measures against static discharges. Storage tanks and other containers must be grounded. Do not smoke, use naked flames or other sources of ignition. Do not eat, drink or smoke when using the product. Observe good industrial hygiene practices.

STORAGE PRECAUTIONS

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep away from heat, sparks and open flame.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m ³	ST - ppm	ST - mg/m ³
ETHANOL	WEL	1000 ppm	1920 mg/m ³		
ISOBUTYL METHYL KETONE	WEL	50 ppm(Sk)	208 mg/m ³ (Sk)	100 ppm(Sk)	416 mg/m ³ (Sk)
PHENOL	WEL	2 ppm(Sk)			
PROPAN-2-OL	WEL	400 ppm	999 mg/m ³	500 ppm	1250 mg/m ³
TOLUENE	WEL	50 ppm(Sk)	191 mg/m ³ (Sk)	150 ppm(Sk)	574 mg/m ³ (Sk)

PROTECTIVE EQUIPMENT



PROCESS CONDITIONS

Provide eyewash, quick drench.

ENGINEERING MEASURES

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined workplace exposure limit is not exceeded.

RESPIRATORY EQUIPMENT

In case of inadequate ventilation or when the product is heated, use suitable respiratory equipment with gas filter (type A2).

HAND PROTECTION

Use protective gloves made of: Rubber or plastic.

EYE PROTECTION

Wear approved chemical safety goggles where eye exposure is reasonably probable.

FLEXANE PRIMER FL-10**HYGIENE MEASURES**

Keep away from food, drink and animal feeding stuffs. Good personal hygiene is necessary. Wash hands and contaminated areas with water and soap before leaving the work site. Do not eat, drink or smoke when using the product. Change work clothing daily before leaving work place.

SKIN PROTECTION

Protection suit must be worn.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid		
COLOUR	Blue		
ODOUR	Solvent.		
SOLUBILITY	Soluble in water		
BOILING POINT (°C)	90.5	RELATIVE DENSITY	0.8 20 °C
VAPOUR DENSITY (air=1)	>1	VAPOUR PRESSURE	13 mmHg 20
EVAPORATION RATE	>1 (butyl acetate =1)	VOLATILE BY VOL. (%)	80
pH-VALUE, CONC. SOLUTION	7 @ 20 °C	FLASH POINT (°C)	12.8
FLAMMABILITY LIMIT - LOWER(%)	1.3	FLAMMABILITY LIMIT - UPPER(%)	8.0

10 STABILITY AND REACTIVITY**STABILITY**

Stable under normal temperature conditions and recommended use.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition.

MATERIALS TO AVOID

Avoid contact with: Strong acids. Bases, alkalies (inorganic). Bases, alkalies (organic). Strong oxidising agents. Amines.

HAZARDOUS DECOMPOSITION PRODUCTS

Fire or high temperatures create: Nitrous gases (NOx). Oxides of: Carbon monoxide (CO). Carbon dioxide (CO₂). Vapours/gases/fumes of: Ammonia or amines.

11 TOXICOLOGICAL INFORMATION**INHALATION**

Harmful by inhalation. Irritating to respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Contains organic solvents which in case of overexposure may depress the central nervous system causing dizziness and intoxication.

INGESTION

Harmful if swallowed. May cause nausea, headache, dizziness and intoxication.

SKIN CONTACT

Harmful in contact with skin. Irritating to skin. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. Risk of sensitisation or allergic reactions among sensitive individuals.

EYE CONTACT

May cause severe irritation to eyes.

HEALTH WARNINGS

Prolonged and repeated contact with solvents over a long period may lead to permanent health problems.

TARGET ORGANS

Central nervous system. Kidneys. Liver. Respiratory system, lungs. Skin.

Name	TOLUENE
Toxic Dose 1 - LD 50	5000 mg/kg (oral rat)
Name	PROPAN-2-OL
Toxic Dose 1 - LD 50	5054 mg/kg (oral rat)
Toxic Dose 2 - LD 50	3600 mg/kg (oral-mouse)
Name	ISOBUTYL METHYL KETONE
Toxic Dose 1 - LD 50	2080 mg/kg (oral rat)
Toxic Conc. - LC 50	8000 ppm/4h (inh-rat)

FLEXANE PRIMER FL-10

12 ECOLOGICAL INFORMATION

ECOTOXICITY

EC50/48h/Daphnia = 1550 mg/l

EC 50, 48 Hrs, DAPHNIA, mg/l MIBK 24h EC-50 1150 mg/l

MOBILITY

Do not discharge into drains, water courses or onto the ground.

DEGRADABILITY

MIBK - BOD-5=1.94-2.06goxygen/g

WATER HAZARD CLASSIFICATION

WGK 2

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

WASTE CLASS

08 04 99

14 TRANSPORT INFORMATION



UK ROAD CLASS	3		
PROPER SHIPPING NAME	FLAMMABLE LIQUID, N.O.S. (TOLUENE, ISOBUTYL METHYL KETONE)		
UN NO. ROAD	1993	UK ROAD PACK GR.	II
ADR CLASS NO.	3	ADR CLASS	Class 3: Flammable liquids.
ADR PACK GROUP	II	HAZARD No. (ADR)	33
ADR LABEL NO.	3	HAZCHEM CODE	3YE
CEFIC TEC(R) NO.	30GF1-I+II, 30GF1-sp	RID CLASS NO.	3
RID PACK GROUP	II	UN NO. SEA	1993
IMDG CLASS	3	IMDG PAGE NO.	3
IMDG PACK GR.	II	EMS	F-E, S-E
MFAG	See Guide	MARINE POLLUTANT	No.
UN NO. AIR	1993	AIR CLASS	3
AIR PACK GR.	II		

15 REGULATORY INFORMATION

LABELLING



Harmful



Highly Flammable

CONTAINS

ISOBUTYL METHYL KETONE
 PHENOL
 TOLUENE

FLEXANE PRIMER FL-10

RISK PHRASES

R20/21/22 Harmful by inhalation, in contact with skin and if swallowed.
 R11 Highly flammable.
 R36/37/38 Irritating to eyes, respiratory system and skin.

SAFETY PHRASES

S7/9 Keep container tightly closed and in a well-ventilated place.
 S16 Keep away from sources of ignition - No smoking.
 S23 Do not breathe vapour/spray.
 S24/25 Avoid contact with skin and eyes.
 S28 After contact with skin, wash immediately with plenty of water.
 S29 Do not empty into drains.
 S33 Take precautionary measures against static discharges.
 S45 In case of accident or if you feel unwell, seek medical advice immediately (show label where possible).

16 OTHER INFORMATION

REVISION DATE 04/11/2005
 REV. NO./REPL. SDS GENERATED 5
 DATE 18.01.2005

RISK PHRASES IN FULL

R11 Highly flammable.
 R20 Harmful by inhalation.
 R23/24/25 Toxic by inhalation, in contact with skin and if swallowed.
 R34 Causes burns.
 R36 Irritating to eyes.
 R36/37 Irritating to eyes and respiratory system.
 R38 Irritating to skin.
 R48/20 Harmful: danger of serious damage to health by prolonged exposure through inhalation.
 R48/20/21/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation, in contact with skin and if swallowed.
 R63 Possible risk of harm to the unborn child.
 R65 Harmful: may cause lung damage if swallowed.
 R66 Repeated exposure may cause skin dryness or cracking.
 R67 Vapours may cause drowsiness and dizziness.
 R68 Possible risk of irreversible effects.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.