


SMF950



Magnetic-inductive flow meter

SMGX2KGFFRKG/UST



Product characteristics				
Measuring range	100...10000 l/min	6...600 m³/h	26...2642 gpm	0.31...30.94 ft/s
Nominal diameter	DN150 (6")			
Process connection	ifm-specific device flange			
Application				
Special feature	Gold-plated contacts			
Application	food and beverage industry			
Media	conductive liquids; water; hydrous media			
Note on media	food products such as beer, milk, fruit juices, soft drinks, ketchup, yoghurt, yoghurt toppings, ice cream			
	conductivity: ≥ 5 µS/cm			
Medium temperature	[°C]	-20...150		
Min. burst pressure	24 bar	348 psi	2.4 MPa	
Pressure rating	16 bar	232 psi	1.6 MPa	
Electrical data				
Operating voltage	[V]	18...32 DC		
Current consumption	[mA]	250; (24 V)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	< 5		
Measuring principle		magnetic-inductive		



Magnetic-inductive flow meter

SMGX2KGFFRKG/UST

Inputs / outputs					
Total number of inputs and outputs		2			
Inputs					
Inputs		OUT2	external totaliser reset		
Outputs					
Total number of outputs		2			
Output signal		OUT1	pulse signal; totaliser switching signal; diagnostic signal; IO-Link		
		OUT2	analogue signal; pulse signal; totaliser switching signal; diagnostic signal		
Electrical design		PNP/NPN			
Pulse output		flow rate meter			
Short-circuit protection		yes			
Type of short-circuit protection		pulsed			
Overload protection		yes			
Analogue					
Number of analogue outputs		1			
Analogue current output [mA]		4...20; (skalierbar)			
Max. load [Ω]		500			
Resolution of analogue output		0.38 µA			
Digital					
Number of digital outputs		2			
Max. voltage drop switching output DC [V]		2			
Permanent current rating of switching output DC [mA]		100			
Switching frequency DC [Hz]		0...10000			
Measuring/setting range					
Measuring range		100...10000 l/min	6...600 m³/h	26...2642 gpm	0.31...30.94 ft/s
Note on factory setting		0...160,0 m³/h			
Analogue start point ASP		-10000...8000 l/min	-600...480 m³/h	-2642...2113 gpm	-30.94...24.75 ft/s
Analogue end point AEP		-8000...10000 l/min	-480...600 m³/h	-2113...2642 gpm	-24.75...30.94 ft/s
Low flow cut-off LFC		0...8000 l/min	0...480 m³/h	0...2113 gpm	0...24.75 ft/s
Pulse length [s]		0.00005...2			
Pulse value		0.017...99999000 l			
Temperature monitoring					
Measuring range		-20...150 °C		-4...302 °F	
Analogue start point		-20...116 °C		-4...240.8 °F	
Analogue end point		14...150 °C		57.2...302 °F	
Conductivity monitoring					
Measuring range [µS/cm]		100...100000			
Analogue start point [µS/cm]		0...80000			
Analogue end point [µS/cm]		20000...100000			



Magnetic-inductive flow meter

SMGX2KGFFRKG/UST

Accuracy / deviations		
Volumetric flow monitoring		
Accuracy (in the measuring range)	with optional factory calibration (availability is being planned)	± (0,2 % MW + 2 mm/s)
	standard	± (0,5 % MW + 1,5 mm/s)
Repeatability	0,1% MW	
Temperature monitoring		
Accuracy	[K]	± 1 (v > 0,5 m/s)
Repeatability	[K]	± 0,5 (v > 0,5 m/s)
Conductivity monitoring		
Accuracy (in the measuring range)	in the range of 100...20000 µS/cm	±10% MW
	in the range of 20000...100000 µS/cm	±20% MW
Repeatability	± 5% MW	
Response times		
Volumetric flow monitoring		
Response time	[s]	< 0.3
Damping process value dAP	[s]	0...5
Temperature monitoring		
Response time	[s]	< 3; (v > 0,5 m/s)
Conductivity monitoring		
Response time	[s]	< 2
Software / programming		
Diagnostic functions	direction of flow detection; liquid detection	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1.3	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor - SSP 4.3.4	Measuring and Switching Sensor, floating point, 4 channel
	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
	Extension	Sensor Control Wide
	Extension	Quantity detection, switches when value exceeds the setpoint
	Function	Locator
	Function	ProductURI
SIO mode	yes	
Required master port type	A	
Process data analogue	6	
Process data binary	8	
Min. process cycle time	[ms]	1.9



Magnetic-inductive flow meter

SMGX2KGFFRKG/UST

IO-Link process data (cyclical)	function	bit length
	totaliser	32
	flow	32
	temperature	32
	conductivity	32
	status	4
	binary switching information	8
IO-Link functions (acyclical)	direction of flow detection; totaliser; memory; operating hours counter; internal temperature; simulation function	
Supported DeviceIDs	Type of operation	DeviceID
	default	1809

Operating conditions		
Ambient temperature	-20...65 °C	-4...149 °F
Storage temperature	-20...80 °C	-4...176 °F
Protection	IP 67; IP 69; (to DIN EN 60529)	

Tests / approvals		
EMC	DIN 61326-1	
Shock resistance	DIN IEC 68-2-27	20 g (18ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000Hz)
MTTF [years]		83
UL approval	UL approval no.	I032
	File number UL	E174189
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]		20800
Housing		cylindrical
Inlet pipe length		5 x DN
Outlet pipe length		2 x DN
Dimensions [mm]		Ø 255 / L = 200
Materials	housing: stainless steel (316L/1.4404); flange: stainless steel (304/1.4301); electronics fixture: stainless steel (304/1.4301); electronics: stainless steel (316L/1.4404); LED ring: PP	
Materials (wetted parts)	Pipe section: PFA; electrodes: stainless steel (316L/1.4435)	
Nominal diameter		DN150 (6")
Process connection		ifm-specific device flange
Surface characteristics Ra/Rz of the wetted parts		Ra < 0.4 µm

Displays / operating elements		
Display	operating status	LED ring, three-colour
Factory setting	m³/h; °C; µS/cm	

SMF950



Magnetic-inductive flow meter

SMGX2KGFFRKG/UST


Remarks	
Remarks	MW = measured value
	MEW = Final value of the measuring range
	pulse and totaliser signal are only available for one of the two outputs
	reference conditions (1/2): water (free of gas bubbles), 15...35 °C, process connection: DIN32676 series A, pipe standard suitable for process connection
	reference conditions (2/2): inlet pipe length 10xDN, outlet pipe length 5xDN, device settling time: 30 minutes, device orientation: horizontal, display orientation: up
	accuracy specifications according to factory certificate on delivery
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection



1	L+	
2	MP2	DO2, AO, reset
3	L-	
4	MP1	DO1, IO-Link

AO: analogue output; DO: digital output; MP: multi-function connection