# General Purpose Relay G7J

- Ideal for 3-phase motor control applications and resistive and inductive loads.
- No contact chattering for momentary voltage drops up to 50% of rated voltage.
- Withstands more than 4 kV between contacts that are of different polarity and between the coil and contacts.
- Flame-resistant materials (UL94V-0) used for all insulation.
- Push-to-test button on all models lets user check contact operation.
- Class B coil insulation available.







## **Ordering Information**

To Order: Select the part number and add the desired coil voltage rating (e.g., G7J-3A1B-B-AC100/120).

Туре	Contact form	Model			
		Quick-connect terminal	Screw terminal	PCB terminal	
PCB mounting	4PST-NO	_	_	G7J-4A-P	
	3PST-NO/SPST-NC	_	_	G7J-3A1B-P	
	DPST-NO/DPST-NC	_	_	G7J-2A2B-P	
W-bracket	4PST-NO	G7J-4A-T	G7J-4A-B		
(see note)	3PST-NO/SPST-NC	G7J-3A1B-T	G7J-3A1B-B		
	DPST-NO/DPST-NC	G7J-2A2B-T	G7J-2A2B-B		

Note: The G7J-B relays require a W-bracket for mounting. Order the bracket separately below. To order a relay and bracket packed together, add "-W1" to the part number before the coil voltage suffix. For example, G7J-2A2B-B-W1-AC100/120.

#### **■** Accessories

Types	Applicable relays	Model	
W-brackets	G7J-4A-B, G7J-3A1B-B, G7J-2A2B-B	R99-04-FOR-G5F	

#### **■** Typical Applications

Compressors for air conditioners and heater switching controllers.

Switching controllers for power tools or motors.

Lamp controls, motor drivers, and power supply switching controllers in copy machines, facsimile machines, and other office equipment.

Power controllers for packers or food processing equipment.

Power controllers for inverters.

# **Specifications**

#### **■** Contact Data

Load	Resistive load (p.f. = 1)				
	NO	NC			
Rated load	25 A, 220 VAC (24 A, 230 VAC), 25 A, 30 VDC	8 A, 220 VAC (7.5 A, 230 VAC), 8 A, 30 VDC			
Rated carry current	25 A	8 A			
Max. switching voltage	250 VAC,125 VDC				
Max. switching current	25 A	8 A			
Max. switching capacity	5,500 VA, 750 W DC 1,760 VA, 240 W DC				
Min. permissible load 100 mA, 24 VDC at 120 operations/minute, 23°C (73°F) ambient temperature)					

## **■** Coil Data

#### **AC**

Coil	Rated voltage	Rated	Coil	Must operate	Must release	Max. voltage	Power
voltage	(VAC)	current (mA) resistance (Ω)		% of rated voltage			consumption
24	24	75	_	75% max.	15% min.	110%	Approx.1.8
50	50	36	_				to 2.6 VA
100/120	100 to 120	18 to 21.60	_	75 volts	18 volts	132 volts	
200/240	200 to 240	9 to 10.80	_	150 volts	36 volts	264 volts	]

#### <u>DC</u>


Coil	Rated voltage	Rated	Coil	Must operate	Must release	Max. voltage	Power
voltage (VDC) c		current (mA)	current (mA) resistance (Ω)	% of rated voltage			consumption
12	12	167	72	75% max.	10% min.	110%	Approx. 2.0 W
24	24	83	288	]			
48	48	42	1150	]			
100	100	20	5000	]			
110	110	18	6050				

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C (73°F) with tolerances of +15%/-20% for AC rated current and ±15% for DC coil resistance.

<sup>2.</sup> Performance characteristic data are measured at a coil temperature of 23°C (73°F).


#### **■** Coil Internal Circuit

#### **AC** operating coil




The G7J incorporates a bridge rectifier circuit in the AC coil versions that prevents contact chatter or dropout during a voltage drop. This circuit allows the relays to withstand, with no vibration or shock, voltage drops to the coil of up to 50% of the rated coil voltage for one second maximum.

#### **DC** operating coil



As a rule, either a DC battery or a DC power supply with a maximum of 5% ripple must be used for the operating voltage for DC relays. Before using a rectified AC supply, confirm that the ripple is not greater than 5%. Ripple greater than this can lead to variations in the operating and reset voltages. As excessive ripple can generate pulses, the insertion of a smoothing capacitor is recommended as shown below.



E max.:Maximum ripple E min.:Minimum ripple

E mean: Mean DC voltage value

When driving the coil with a transistor, check the leakage current and connect a bleeder resistor if necessary.


#### **■** Characteristics

Contact resistance		50 mΩmax.			
Operating time		50 ms max.			
Release time		50 ms max.			
Operating frequency	Mechanical	1,800 operations/hour max.			
	Electrical	800 operations/hour max.			
Insulation resistance		1,000 MΩ minimum at 500 VDC			
Dielectric strength		4,000 VAC, 50/60 Hz for 1 minute between coil and contacts			
		4,000 VAC, 50/60 Hz for 1 minute between contacts of different polarity			
		2,000 VAC, 50/60 Hz for 1 minute between contacts of the same polarity			
Impulse withstand volt	tage	10,000 V between coil and contact with 1.2 x 50 μs impulse wave			
Vibration	Mechanical durability	10 to 55 Hz, 1.50 mm (0.06 in) double amplitude			
	Malfunction durability	NO: 10 to 55 Hz, 1.50 mm (0.06 in) double amplitude			
		NC: 10 to 26 Hz, 1.50 mm (0.06 in) double amplitude			
Shock	Mechanical durability	1000 m/s <sup>2</sup> (Approx. 100 G)			
	Malfunction durability	y NO: 100 m/s² (Approx. 10 G)			
		NC: 20 m/s <sup>2</sup> (Approx. 2 G)			
Service life	Mechanical	1 million operations minimum at 1,800 operations/hour			
	Electrical	100,000 operations minimum at 1,800 operations/hour at rated load			
Ambient temperature	re Operating -25° to 60°C (-13° to 140°F) with no icing				
Humidity	Operating	35% to 85% RH			
Weight	PCB terminal	Approx. 140 g (4.90 oz.)			
	Screw terminal	Approx. 165 g (5.80 oz.)			


Note: Data shown are of initial value.

#### **■** Characteristic Data

#### Maximum switching capacity



#### **Electrical service life**




## **Dimensions**


Unit: mm (inch)

#### **■** Relays

PCB Terminals with PCB Mounting G7J-4A-P, G7J-3A1B-P, G7J-2A2B-P




Screw Terminals (requires W-bracket for mounting) G7J-4A-B, G7J-3A1B-B, G7J-2A2B-B



#### **■** Accessories

W-Bracket for G7J-B Relays with Screw Terminals R99-04-FOR-G5F



## ■ Terminal Arrangement – Internal Connections

