# M18 ONEHCCT60-202C

## M18™ FORCE LOGIC™ HYDRAULIC 60 KN CABLE CRIMPER

- FORCE LOGIC™ hydraulic cable crimper crimps connectors up to 300 mm² in less than 5 seconds with 60 kN of force
- Easy die alignment and linear movement ensure most uniform crimp results
- Improved ergonomics and slim handle design provide for a comfortable one-handed operation
- Easy to reach electronic release button within grip area allows users to reset a crimp conveniently at any time
- The quick latching head is rotatable by 350° and has an integrated light which perfectly illuminates the crimp surface
- PFM™ (Predictive Force Monitoring): Automatically modifies output based on connector, ensuring optimal pressure every time and visualises with a green light
- Allows crimping of connectors up to 300 mm² in copper and aluminium
- Universal die reception is compatible with MILWAUKEE® 22-series die range and most common 60 kN U-dies (C shaped dies) on the market
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality. The reporting function delivers a complete tool activity and accuracy protocol
- Pre-crimp battery check automatically ensures enough charge to complete each crimp
- Sealed electronics resist harsh environments with dirt, dust and moisture




REDLITHIUM™




| | |
|---|---|
| Crimping force (kN) | 60 |
| Crimping range ($mm^2$) | 6 - 300 |
| Crimping time (s) | 5 |
| Crimps per battery | >150 on a 50 $mm^2$ copper connector |
| Kit included | 2 x M18 B2 Battery packs, M12-18 C Charger, Kitbox |
| Weight with battery pack (EPTA) (kg) | 3.8 (M18 B2) |
| Article Number | 4933479684 |