

Label - MM-EML (EX18)R C1 TR/BK - 1116130

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Label, Roll, transparent/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 16 mm

Product Description


The MM-EML... polyester self-adhesive labels are available as continuous media for equipment marking.

Your advantages

- The material is cUL certified
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 041151
GTIN	4063151041151
Weight per Piece (excluding packing)	58.000 g
Custom tariff number	96121020
Country of origin	China
Sales Key	BG241E

Technical data

Dimensions

Length (b)	8 m
Width (a)	18 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

Label - MM-EML (EX18)R C1 TR/BK - 1116130

Technical data

Ambient conditions

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---

General

Color	transparent/black
Components	free from silicone, halogen, and cadmium
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	adhesive
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 11.0	27281103
eCl@ss 9.0	27400629

ETIM

ETIM 7.0	EC001288
----------	----------

Approvals

Approvals

Label - MM-EML (EX18)R C1 TR/BK - 1116130


Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	MH48542
------------------	---	---	---------

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>