




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	4
Number of Loaded Positions	4
Number of Power Positions	4
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical



Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

PCB Retention Feature Material	Phosphor Bronze
PCB Retention Feature Plating Material	Tin
Primary Product Color	Black

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 2.54 µm[50 – 100 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Size	.64mm
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Mating Square Post Dimension	.64 mm[.025 in]
PCB Contact Termination Area Plating Material Thickness	2.54 – 7.62 µm[100 – 300 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	4.15 mm[.163 in]
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Tab
Contact Current Rating (Max)	5 A

Termination Features

Termination Post & Tail Length	3.18 mm[.125 in]
Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With



Mating Alignment Type	Polarization
PCB Mount Retention Type	Hold-Down
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Mating Entry Location	Top
Housing Material	High Temperature Nylon
Centerline (Pitch)	3 mm [.118 in]

Dimensions

Connector Width	3.86 mm [.152 in]
PCB Thickness (Recommended)	1.57 mm [.062 in]
Connector Height	9.24 mm [.364 in]
Connector Length	16.14 mm [.635 in]

Usage Conditions

Operating Temperature (Max)	105 °C [221 °F]
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Power

Industry Standards

Compatible With Agency/Standards Products	CNR, USR
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	210
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-1586842-6
16P MICRO MNL ASY,VRT,REV REEL

TE Part # 1-2029037-0
MICRO MNL HDR ASY SR AU LF SPC

TE Part # 2029076-2
2P MICRO MNL 1R RA HDR ASY NAT

TE Part # 2008570-4
4 POS MICRO MNL, SIDE LATCH, B

TE Part # 1445022-4
MICRO MNL RFCEPT HSG SINGLE R

TE Part # 1586842-6
6P MICRO MNL ASY,VRT,REV REEL

TE Part # 2-1586842-0
20P MICRO MNL ASY,VRT,REV REEL

TE Part # 2008571-4
4 POS MICRO MNL, TOP LATCH, BL





TE Part # 2029047-4
4P MICRO MNL RCPT HSG SR SIDE



TE Part # 2-1445094-4
MICRO MNL HDR ASSY S/ROW AU LF




TE Part # 1586842-2
2P MICRO MNL ASY,VRT,REV REEL



TE Part # 2315752-4
4P, MICRO MNL RCPT HSG SINGLE ROW, V0 GW



TE Part # 2029102-4
4P MICRO MNL RCPT SR SIDE WHT



TE Part # 1586842-4
4P MICRO MNL ASY,VRT,REV REEL




TE Part # 2-1445084-5
micro mnl hdr assy s/row au lf

Also in the Series | Micro MATE-N-LOK



Connector Contacts(27)



PCB Headers & Receptacles(371)



Power Contacts(27)



Rectangular Connector Housings(98)



Rectangular Power Connectors(469)




Standard Rectangular Connectors(98)



Wire-to-Board Headers & Receptacles (371)

Customers Also Bought



TE Part #2-520184-4
ULTRAFAST 250 ASSY REC 22-18 TPBR LP



TE Part #320554
PIDG R 22-16 COMM 22-18 MIL 8



TE Part #MS580314BA01-00
MS5803-14BA01 DIGIT PRESSURE SENSOR TUBE



TE Part #165046
PIDG WIRE PIN






TE Part #794610-1
MICRO MNL RPT CNT,LS PC,TIN




TE Part #1375820-7
CST-100 II HOUSING 7 POS



TE Part #640905-1
RECEPT,PIDG FASTON 16-14 250



TE Part #8-215083-4
MICRO-MATCH MOW.14P



TE Part #643077-7
07P MTA100 MOLDED COVER F/T



TE Part #969973-2
2x2P HV100 REC. CON, SMD, GOLD, BLISTER

Documents

Product Drawings

MICRO MNL HDR ASY SR AU LF SPC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2029037-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2029037-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2029037-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MICRO MATE-N-LOK CONNECTOR SYSTEM

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report



English