

SELOS WTN · 2.5 mm² MULTI-TIER TERMINAL

WTN 2.5 E3 VB...

- Screw connection / mounting on DIN rail TH35
- Nominal cross section 2.5 mm²
- Screwdriver 0.6x3.5
- Connection capacity: 2 wires, equal size 0.34 – 1.5 mm²




Description	Type	Part No.	Std. Pack
Multi-Tier Terminal	black	WTN 2.5 E3 VB	5D.S03.6855.1
Multi-Tier Terminal	red	WTN 2.5 E3 VB RT	5D.S03.6855.5
Multi-Tier Terminal	blue	WTN 2.5 E3 VB BL	5D.S03.6855.6

GENERAL DATA		
Width / length / height, incl. TS 7.5	5.1 mm / 90.7 mm / 76 mm	
Wire strip length	10 mm	
TECHNICAL DATA	IEC	UL 1059 / CSA 158
Cross section fine-stranded	0.34 - 2.5 mm ²	
Cross section solid/stranded	0.34 - 4 mm ²	
Cross section, AWG (sol/str)	22-12	
Rated current	24 A	20 A
Rated voltage	1000 V	600 V
Rated impulse voltage	8 kV	
Pollution degree	3	

Accessories	Type	Part No.	Std. Pack
End Plate	grey	APWTN 2.5 E3	0D.S03.2455.0

WTN 2.5 E3 ...

- Screw connection / mounting on DIN rail TH35
- Nominal cross section 2.5 mm²
- Screwdriver 0.6x3.5
- Connection capacity: 2 wires, equal size 0.34 – 1.5 mm²



Description	Type	Part No.	Std. Pack
Multi-Tier Terminal	grey	WTN 2.5 E3	5D.S03.7155.0
Multi-Tier Terminal	red	WTN 2.5 E3 RT	5D.S03.7155.5
Multi-Tier Terminal	blue	WTN 2.5 E3 BL	5D.S03.7155.6

GENERAL DATA		
Width / length / height, incl. TS 7.5	5.1 mm / 90.7 mm / 76 mm	
Wire strip length	10 mm	
TECHNICAL DATA	IEC	UL 1059 / CSA 158
Cross section fine-stranded	0.34 - 2.5 mm ²	
Cross section solid/stranded	0.34 - 4 mm ²	
Cross section, AWG (sol/str)	22-12	
Rated current	24 A	20 A
Rated voltage	1000 V	600 V
Rated impulse voltage	8 kV	
Pollution degree	3	

Accessories	Type	Part No.	Std. Pack
End Plate	grey	APWTN 2.5 E3	0D.S03.2455.0

WTN 2.5 EL PE

- Screw connection / mounting on DIN rail TH35
- Nominal cross section 2.5 mm²
- Screwdriver 0.6x3.5
- Connection capacity: 2 wires, equal size 0.34 – 2.5 mm²



Description	Type	Part No.	Std. Pack
Ground Terminal	grey/green/yellow	WTN 2.5 EL PE	5D.S03.9755.0

GENERAL DATA		
Width / length / height, incl. TS 7.5	5.1 mm / 71.5 mm / 60 mm	
Wire strip length	10 mm	
TECHNICAL DATA	IEC	UL 1059 / CSA 158
Cross section fine-stranded	0.34 - 2.5 mm ²	
Cross section solid/stranded	0.34 - 4 mm ²	
Cross section, AWG (sol/str)	22-12	
Rated current	24 A	20 A upper Levels
Rated voltage	800 V	600 V
Rated impulse voltage	8 kV	
Pollution degree	3	

Accessories	Type	Part No.	Std. Pack
End Plate	grey	APWTN 2.5/4 E	0D.S03.2355.0