




Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories >

enetSEAL+ Ethernet Connector Accessories



Primary Product Color: **Brown**
Primary Product Material: **PBT GF**
Automotive Connector Accessory Type: **Mounting Clip**
Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

[All enetSEAL+ Ethernet Connector Accessories \(5\)](#)

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Clip
-------------------------------------	---------------

Body Features

Primary Product Color	Brown
Primary Product Material	PBT GF

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AI5-EH
enetSEAL+ Ethernet Connector Housings



TE Part # 2325102-1
2POS,TAB1.2X0.6,HDR ASSY,180DEG,SLDR

Also in the Series | enetSEAL+



Automotive Connector Caps & Covers (1)



Automotive Headers(4)




Automotive Housings(4)



Infotainment & Multimedia Cable Assemblies(8)




Other Automotive Connector Accessories(3)



PCB Headers & Receptacles(4)




Rectangular Power Connectors(4)



Wire-to-Board Headers & Receptacles (4)

Customers Also Bought



TE Part #1670144-3
MCON 1.2 CB REC SRC AG



TE Part #DT06-2S-E003
PLG, 2P, GRY, N, CAP



TE Part #CAT-AI5-EH
enetSEAL+ Ethernet Connector Housings



TE Part #2325103-7
2POS,TAB1.2X0.6,HDR ASSY,180DEG, SLDR



TE Part #2325098-4
MNTG CLIP,ENETSEAL PLUS



TE Part #DTM12P-DC
PROTECT CVR, 12P, REC, GRY, DTM

Documents

Product Drawings
MNTG CLIP,ENETSEAL PLUS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2325098-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2325098-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2325098-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
DATA CONNECTIVITY SOLUTIONS

English

Product Specifications
Application Specification

English