









NK Series Microminiature Slide Switches

SPECIFICATIONS	FEATURES
<p>Contact rating: 500 mA at 12V Initial contact resistance: 20 milliohms max. Insulation resistance: 10,000 MΩ min. at 500VDC Dielectric strength: 250 Vrms between terminals 2000 Vrms between adjacent poles placed side by side Electrical life: 2,000 cycles min. Operating temperature range: -40°C to +85°C Solder heat resistance: 250°C max. for 5 seconds Washing not recommended</p>	<ul style="list-style-type: none"> ● Cost effective. ● Through-hole round terminals, straight or right angle. ● Stackable in X & Y directions (with straight terminals).
MATERIALS	
	<p>Contacts & terminals: Gold over nickel plated Case: Glass filled polyamide (UL94V-0) Actuator: Glass filled polyamide (UL94V-0)</p>

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

MODEL NO.	1P1T		
NK236			
	 <p>● = COMMON</p>		
VERTICAL ACTUATOR	SCHEMATIC	MECHANICAL OUTLINE	P.C. BOARD LAYOUT

MODEL NO.	1P1T		
NK236W			
<p style="color: red; font-weight: bold; font-size: 1.2em;">New!</p> 	 <p>● = COMMON</p>		
RIGHT ANGLE TERMINALS	SCHEMATIC	MECHANICAL OUTLINE	P.C. BOARD LAYOUT

EXAMPLE OF PRINTED CIRCUIT BOARD LAYOUT FOR STACKING UNITS

Pitch = .100" (2.54mm)

