

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
FT	60		C	REV; EC 0210-0674-95	10-25-95	LM/UTA
			D	REV PER EC 0320-68-97	06 MAR 97	MBMM
			E	REV PER EC 061C-95-98	14 JUL 98	COMC

- 1
- ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2
- MATERIAL: 2.54μm [.000100] MINIMUM TIN PLATED COPPER ALLOY 0.74-0.79 [.030±.001] THICK.
3.
- WIRE BARREL ACCEPTS ONE 14, 16 OR 18 AWG STRANDED COPPER WIRE.
- 4
- CONTACTS ON REEL SHALL BE CRIMPED USING APPLICATOR TOOL PN 567403.
- 5
- LOOSE PIECE CONTACTS SHALL BE CRIMPED USING TOOLS AND DIE SETS LISTED BELOW.
HAND TOOL: AMP PART NO. 69710
PNEUMATIC TOOL: AMP PART NO. 69365
DIE SET 14 AWG: AMP PART NO. 58492-1
DIE SET 16-18 AWG: AMP PART NO. 58493-1



REEL 4	556883-2
LOOSE PIECE 5	556883-1
DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN D. STRAUSSER 5-29-91	AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK B. FOX 8-23-91			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. MILLER 8-26-91	NAME CONTACT, DUAL BEAM, 14-18 AWG, WTB, AMPINNERGY™		
1 PLC ± 1 2 PLC ± 1 3 PLC ± 1 4 PLC ± 1 ANGLES ± FINISH 2		PRODUCT SPEC 108-1349 APPLICATION SPEC 114-6044 WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-556883
MATERIAL 2			SCALE 4:1	SHEET 1 OF 1	REV E
CUSTOMER DRAWING					