

ZN-DT350APE

540 TVL Impact Resistant MPEG-4 Colour IP Dome Camera



ZN-DT350APE

Key Features

- ▶ MPEG-4 Compression
- ▶ Super High Resolution of 540TVL
- ▶ 4-9mm Varifocal AI Lens
- ▶ D1, 2CIF, CIF, qcif
- ▶ 25 ips@D1
- ▶ Colour/Mono
- ▶ On Screen Display
- ▶ Audio G.711 Format
- ▶ Surface or Flush Mount
- ▶ Digital Alarm In/Out

V1.01

ZN-DT350APE


Super high resolution mini IP dome camera

Specifications

Description / Model	ZN-D310APE
CAMERA MODULE	
Image Sensor	Sony 1/3" Super HAD CCD
Effective Pixels	752 x 582 (PAL)
Scanning System	2:1 Interlace
Horizontal Resolution	540 TVL
Minimum Illumination	0.5 Lux (30 IRE): Day & Night Off (Colour)
Lens	4 ~ 9 mm Vari-focal Auto Iris
Colour/Mono	Electronic Day/Night
Function Key	AGC, EE / AI, BLC, FLK, Gamma, Mirror
VIDEO	
Compression Format	MPEG-4, MJPEG Selectable
Resolution	D1, 2CIF, CIF, QCIF
Compression FPS	25/30 fps@D1
Deinterlacing	Yes
Motion Detection	Yes
Burnt-in Text (Digital)	Yes
Stream Encryption	AES
Output	1 Loop Out (BNC Connector)
AUDIO	
Input	1 channel
Output	1 channel
Compression Format	G.711
FUNCTION	
Digital Input	1 channel
Digital Output	1 channel
RS-485/422	Yes
RS-232C	Yes
Network	10/100 Base-T
Protocol	TCP/IP, UDP/IP, HTTP, RTSP, RTP/UDP, RTP/TCP, SNMP, mDNS, UPnP, SMTP, SOCK, IGMP, DHCP, DDNS
NB. Specification subject to change without notification	

Description / Model	ZN-D310APE
ELECTRICAL	
Power Source	12V DC (DC Jack)
Power over Ethernet	Yes (IEEE 802.3af)
Power Consumption	500 mA (Approx)
Approvals	All A/C driven sources are U/L approved
ENVIRONMENTAL	
Operating Temperature	0°C ~ 60°C (32°F ~ 140°F)
Operating Humidity	Up to 85% RH (Non-condensing)
MECHANICAL	
Material	ABS/Polycarbonate
Colour	White
Dimension	Housing: 140(diam) x 112(H) mm, Dome: 100.0(diam) mm
Weight (Approx)	860 g
WARRANTY	
Warranty Period	3 Years

(Unit: mm)



V1.01