



Connectors > Rectangular Connectors > Standard Rectangular Connectors > AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Connector Assembly**  
Connector System: **Wire-to-Board**  
Number of Positions: **6**  
Centerline (Pitch): **2 mm [ .079 in ]**  
Number of Rows: **1**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

|                                   |                    |
|-----------------------------------|--------------------|
| Connector Product Type            | Connector Assembly |
| Connector System                  | Wire-to-Board      |
| Sealable                          | No                 |
| Connector & Contact Terminates To | Wire & Cable       |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 6 |
| Number of Rows      | 1 |

Contact Features

|                              |     |
|------------------------------|-----|
| Contact Current Rating (Max) | 2 A |
|------------------------------|-----|

Mechanical Attachment

|                         |                            |
|-------------------------|----------------------------|
| Connector Mounting Type | Cable Mount (Free-Hanging) |
|-------------------------|----------------------------|

Housing Features

|                    |               |
|--------------------|---------------|
| Housing Material   | PBT GF        |
| Centerline (Pitch) | 2 mm[.079 in] |

Dimensions

|  |      |
|--|------|
|  | 2 in |
|--|------|



Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -30 – 105 °C[-22 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 4-292254-6  
CT RELAY HDR ASSY 6P YELLOW



TE Part # CAT-3983174-PHBXHK  
CT 2mm Post Header Assembly Box H Kink




TE Part # 4-292170-6  
CT P/HDR ASSY 6P V W/O KINK T




TE Part # CAT-3980407-RHDRRA  
CT 2mm Header Assembly: Right Angle



TE Part # CAT-AM7017-H342  
AMP COMMON TERMINATION HEADERS



TE Part # 4-292161-6  
CT P/HDR ASSY V 6P W/KINK YELL




TE Part # 4-292165-6  
CT P/HDR BOX V 6P T/P YELLOW



TE Part # 292254-6  
CT RELAY HDR ASSY 6P NAT




TE Part # 58074-1  
MTA 50/100/156 MANUAL TOOL FRAME



TE Part # 4-292145-6  
CT P/HDR ASSY V 6P W/O KINK YE




TE Part # CAT-3984552-BHTHVS  
CT Box Header SMT: Vert, Shrouded



TE Part # CAT-3983178-PHBXVD  
CT 2mm Post Header Asmbly: Box V DIP



TE Part # 58372-1  
HEAD (IDC) 2MM C.T. W/O TL




TE Part # 4-292156-6  
CT RELAY HDR ASSY FREE HANGING


Also in the Series | AMP CT



Connector Contacts(8)



Connector Hardware(46)



PCB Headers & Receptacles(756)



Rectangular Connector Housings(72)



Rectangular Power Connectors(906)



Standard Rectangular Connectors(158)



Wire-to-Board Connector Assemblies & Housings(97)



Wire-to-Board Headers & Receptacles (756)

Customers Also Bought





Documents

CAD Files

Customer View Model

ENG\_CVM\_CVM\_4-173977-6\_M.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-173977-6\_M.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-173977-6\_M.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

MINI PRESS CT CONNECTOR (WAS IS-553J)

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

CSA Certificate

English



CSA Certificate

English