




H	12		11		10		9		8		7		6		5		4		3		2		1														
								X= MAKE-FIRST/BREAK-LAST CIRCUIT																													
	MATERIAL NO:	ENG.NUMBER	CKTS	FINISH	RETENTION PEG	DIM A	DIM B	DIM C	CKT 1	CKT 2	CKT 3	CKT 4	CKT 5	CKT 6	CKT 7	CKT 8	CKT 9	CKT 10	CKT 11	CKT 12	CKT 13	CKT 14	CKT 15	CKT 16	CKT 17	CKT 18	CKT 19	CKT 20	CKT 21	CKT 22	CKT 23	CKT 24					
	44428-0432	N/A	04	B	YES	<u>13.00</u> .512	<u>3.00</u> .118	N/A		X																											
	44428-0632	N/A	06	B	YES	<u>16.00</u> .630	<u>6.00</u> .236	N/A					X																								
G	44428-0832	N/A	08	B	YES	<u>19.00</u> .748	<u>9.00</u> .354	<u>4.68</u> .184							X																						
	44428-0833	N/A	08	C	YES	<u>19.00</u> .748	<u>9.00</u> .354	<u>4.68</u> .184								X																					
	44428-1032	N/A	10	B	YES	<u>22.00</u> .866	<u>12.00</u> .472	<u>7.68</u> .302	X	X	X	X	X	X	X	X		X																			
	44428-1037	N/A	10	D	YES	<u>22.00</u> .866	<u>12.00</u> .472	<u>7.68</u> .302				X																									
			12																																		
F	44428-1433	N/A	14	C	YES	<u>28.00</u> 1.102	<u>18.00</u> .709	<u>13.68</u> .539						X								X															
			16																																		
	44428-1831	N/A	18	D	YES	<u>34.00</u> 1.338	<u>24.00</u> .945	<u>19.68</u> .775	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X													
	44428-1833	N/A	18	C	YES	<u>34.00</u> 1.338	<u>24.00</u> .945	<u>19.68</u> .775	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X													
			20																																		
E	44428-2231	N/A	22	D	YES	<u>40.00</u> 1.575	<u>30.00</u> 1.181	<u>25.68</u> 1.011														X	X	X	X	X	X										
	44428-2232	N/A	22	B	YES	<u>40.00</u> 1.575	<u>30.00</u> 1.181	<u>25.68</u> 1.011														X	X	X	X	X	X										
	44428-2233	N/A	22	C	YES	<u>40.00</u> 1.575	<u>30.00</u> 1.181	<u>25.68</u> 1.011														X	X	X	X	X	X										
	225732-2201	44428-22B01-TR	22	B	YES	<u>40.00</u> 1.575	<u>30.00</u> 1.181	<u>25.68</u> 1.011	X	X	X	X	X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X							
	44428-2431	N/A	24	D	YES	<u>43.00</u> 1.693	<u>33.00</u> 1.299	<u>28.68</u> 1.129															X	X	X	X	X	X	X	X							
D									CKT 1	CKT 2	CKT 3	CKT 4	CKT 5	CKT 6	CKT 7	CKT 8	CKT 9	CKT 10	CKT 11	CKT 12	CKT 13	CKT 14	CKT 15	CKT 16	CKT 17	CKT 18	CKT 19	CKT 20	CKT 21	CKT 22	CKT 23	CKT 24					

ENG NUMBER LEGENG:

44428 - 04 A * * - * *

BASE NUMBER

CIRCUIT SIZE

(SEE LEGENG NOTE 1)TYPE


SERIAL NUMBER

PACKAGING

(SEE LEGENG NOTE 2)

LEGENG NOTE:

1. TYPE A= DUAL ROW VERTICAL THROUGH HOLE MF/BL
B= DUAL ROW RIGHT ANGLE THROUGH HOLE MF/BL
C= DUAL ROW VERTICAL SMT MF/BL
D= DUAL ROW RIGHT ANGLE SMT MF/BL
2. PACKAGING TR= TRAY PACKAGING
TP= TAPE REEL PACKAGING
TP1= TAPE REEL WITH PICK UP CAP PACKAGING
FOR VERTICAL TYPE ONLY

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																					
		DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex											
FA = 0 FE = 0 FD = 0		MM/INCH		NTS																			
DIVISIONAL SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 768244 DRWN: ZIXUAQ 2023/07/06 CHK'D: XQZHANG 2023/11/13 APPR: XQZHANG 2023/11/13												MICRO-FIT(3.0) BMI MAKE-FIRST/BREAK-LAST DUAL ROW RIGHT ANGLE HEADER					
			MM	INCH																			
		4 PLACES	±	±																			
		3 PLACES	±	± 0.01																			
		2 PLACES	± 0.25	± 0.015																			
		1 PLACE ± 0.38 ±				INITIAL REVISION:						PRODUCT CUSTOMER DRAWING											
		0 PLACES ±																					
ANGULAR TOL ± 0.5 °				DRWN: DRAWN BY 0099/99/99						DOC NUMBER				DOC TYPE		DOC PART		REVISION					
APPR: APPR BY 0099/99/99				SD-44428-004						PSD				001		B							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER				SHEET NUMBER							
						C-SIZE		44428		SEE CHART		GENERAL MARKET				2 OF 2							

FORMAT: Engleja-massan B-yrstet C REVISJON: 0 DATE: 202-05-01												12	11	10	9	8	7	6	5	4	3	2	1
---	--	--	--	--	--	--	--	--	--	--	--	----	----	----	---	---	---	---	---	---	---	---	---