

LE1M35M7

Enclosed DOL starter, TeSys LE, 16A, 220V AC coil, including 1 LC1K, 2 pushbuttons, yellow indicator

Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1M
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor Earth terminal Neutral terminal
[Ie] rated operational current	16 A AC-3
[Uc] control circuit voltage	220 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O



Complementary

Local signalling	Operating: LED (yellow)
Cable entry number	2 ISO20 top 2 ISO25 top 2 Pg 13 top 2 Pg 21 top 2 ISO20 bottom 2 ISO25 bottom 2 Pg 13 bottom 2 Pg 21 bottom 2 Pg 16 top 2 Pg 16 bottom
Width	78 mm
Height	160 mm
Depth	108 mm
Net weight	0.6 kg

Environment

Material	ABS (acrylonitrile butadiene-styrene)
IP degree of protection	IP65 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment
Product certifications	UKCA

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins