ROHDE & SCHWARZ Make ideas real



## **R&S®Spectrum Rider FPH Spectrum Analyzer** Small form factor to handle big tasks



## The three key Ps for lab and field environments

Performance – excellent DANL and phase noise

Weak signals can be easily captured

Portability - weighs only 2.5 kg

- ► Carrying holster (HA-Z322) to free up hands
- ► Side strap included for easy transportation
- ► Selection of carrying cases available
- Price low starting price and optional software keycode upgrades
- Competitive and attractive price
- ► No downtime, no recalibration needed




For price and more information: www.rohde-schwarz.com/catalog/FPH The perfect choice for

Spectrum clearance	Interference
(5G ready)	hunting
Pulse measurement	EMI debugging and RF design validation


Models	Supporting frequency range	
R&S <sup>®</sup> Spectrum Rider FPH	Default range	Upgrade to
Model .02	5 kHz to 2 GHz	3/4 GHz
Model .06	5 kHz to 6 GHz	8 GHz
Model .13	5 kHz to 13.6 GHz	20 GHz
Model .26	5 kHz to 26.5 GHz	31 GHz

Key specifications	
Frequency	5 kHz to 31 GHz
Resolution bandwidths	1 Hz to 3 MHz
DANL at 3 GHz (preamp on)	< -163 dBm
Phase noise, 100 kHz offset	105 dBc/Hz at $f = 500 \text{ MHz}$
Battery operation time	> 6 hours
Weight	2.5 kg


Your t	penefit	Features
that of handh	/ life twice current eld um analyzers	► > 6 hours battery life
capaci touchs availab	bhone style tive creen; also ole with onal interface	<ul> <li>7 inch antiglare capacitive color touchscreen</li> <li>On-screen keyboard</li> <li>Smartphone-like gestures</li> <li>Adjustable display brightness</li> <li>Large backlit button keypad</li> <li>Multifunction rotary knob</li> </ul>
need; u later w	ng analyzer	<ul> <li>Selection of 2 / 6 / 13.6 / 26.5 GHz base models</li> <li>Frequency upgrade keycode options available for each base model</li> <li>Keycode options for function upgrades</li> </ul>



The analyzer has an innovative fanless concept – part of a rugged design that protects it from dust and water. Designed with power optimization in mind, the R&S<sup>®</sup>Spectrum Rider consumes less power than competitor products and can be operated for a full working day without recharging.



The R&S<sup>®</sup>Spectrum Rider FPH is a high-quality spectrum analyzer. Its favorable price tag lowers the barrier to entry for prospective premium analyzer owners. The unique frequency upgrade concept and software keycode options make it easy to upgrade the instrument.



Performance and features

The R&S<sup>®</sup>Spectrum Rider FPH has exceptional phase noise and DANL to capture known and unknown signals. R&S<sup>®</sup>Spectrum Rider FPH easily measures a wide range of parameters such as total harmonic distortion, occupied bandwidth, output power and channel power, making it the ideal tool for field work.

## Other products to consider

- R&S®NRP power sensors all models up to 110 GHz supported
- R&S<sup>®</sup>FSH when you need digital modulation analysis

## **Ordering information**

ordening information			
Choose your model and frequency			
Base model			
R&S®Spectrum Rider handheld spectrum analyzer, 5 kHz to 2/6/13.6/26.5 GHz	R&S®FPH		
Frequency and preamplifier upgrade for 2 GHz model	l		
Spectrum analyzer frequency upgrade, 2 GHz to 3 GHz	R&S®FPH-B3		
Spectrum analyzer frequency upgrade, 2 GHz to 4 GHz	R&S®FPH-B4		
Preamplifier, 5 kHz to 4 GHz	R&S <sup>®</sup> FPH-B22		
Frequency and preamplifier upgrade for 6 GHz model	l		
Spectrum analyzer frequency upgrade, 6 GHz to 8 GHz	R&S®FPH-B8		
Preamplifier, 5 kHz to 8 GHz	R&S®FPH-B23		
Frequency and preamplifier upgrade for 13.6 GHz mo	quency and preamplifier upgrade for 13.6 GHz model		
Spectrum analyzer frequency upgrade, 13.6 GHz to 20 GHz	R&S®FPH-B20		
Preamplifier, 5 kHz to 20 GHz	R&S <sup>®</sup> FPH-B24		
Frequency and preamplifier upgrade for 26.5 GHz mo	del		
Spectrum analyzer frequency upgrade, 26.5 GHz to 31 GHz	R&S®FPH-B31		
Preamplifier, 5 kHz to 31 GHz	R&S <sup>®</sup> FPH-B25		
Popular options/accessories			
Description			
Power sensor support	R&S <sup>®</sup> FPH-K9		
Channel power meter	R&S <sup>®</sup> FPH-K19		
Pulse measurements with power sensor	R&S <sup>®</sup> FPH-K29		
Interference analysis	R&S <sup>®</sup> FPH-K15		
Signal strength mapping	R&S <sup>®</sup> FPH-K16		

Accessories: All models include a lithium-ion battery pack, side strap for hand, USB cable, power cord and three-year warranty.

Languages supported: English, German, French, Spanish, Russian, simplified and traditional Chinese, Korean and Japanese.

Rohde & Schwarz GmbH & Co. KG | Europe, Africa, Middle East +49 89 4129 12345 | North America 1 888 TEST RSA (1 888 837 87 72) Latin America +1 410 910 79 88 | Asia Pacific +65 65 13 04 88 | China +86 800 810 82 28 / +86 400 650 58 96

www.rohde-schwarz.com | customersupport@rohde-schwarz.com

R&S<sup>®</sup> is a registered trademark of Rohde & Schwarz GmbH & Co. KG | PD 5214.9380.32 | Version 02.10 | April 2020 (as) Trade names are trademarks of the owners | R&S<sup>®</sup>Spectrum Rider FPH | Data without tolerance limits is not binding Subject to change | © 2020 Rohde & Schwarz GmbH & Co. KG | 81671 Munich, Germany