


## FEATURES

- **High thermal conductivity of 1.6 W/mK:** Enhances heat transfer efficiency, reducing the risk of overheating.
- **Wide operating temperature range from -60 °C to 240 °C:** Suitable for various environments and applications.
- **Non-adhesive design:** Allows for easy repositioning and removal without leaving residue.
- **Compact dimensions of 100 mm length and 200 mm width:** Fits a variety of component sizes and configurations.
- **Compliant with ANSI-ESD S20.20:2021, REACH, and RoHS standards:** Ensures safety and environmental compliance.

## RS PRO 100 mm Thermal Conductive Pad, 0.25 mm Thickness

RS Stock No: 625-762



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO thermal conductive pad is designed to efficiently transfer heat between components, ensuring optimal performance and longevity of electronic devices. With its high thermal conductivity, it is ideal for use in applications where effective heat dissipation is crucial.

## General Specifications

Colour	Brick Red
Product Type	Thermal Conductive Pad
Self-Adhesive	No

## Mechanical Specifications

Length	100 mm
Thickness	0.25 mm
Width	200 mm

## Operation Environment Specifications

Maximum Operating Temperature	240 °C
Minimum Operating Temperature	-60 °C

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, REACH, RoHS
---------------------	-----------------------------------

## Thermal Performance Specifications

Thermal Conductivity	1.6 W/mK
----------------------	----------