

Test adapter - PAIS-4-FIX BU - 3032798

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: blue


Your advantages

- ✓ Make contact and latch securely to any point in the function shaft
- ✓ Test adapter for accommodating safety test plugs with a 4 mm diameter

RoHS

COMPLETE RoHS

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 055626 369334 |
| GTIN | 4055626369334 |
| Weight per Piece (excluding packing) | 2.390 g |
| Custom tariff number | 85366990 |
| Country of origin | Poland |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|--------------|---------|
| Height | 53.3 mm |
| Length | 6.5 mm |
| Width | 6 mm |
| Diameter | 5.8 mm |
| Pin diameter | 2.4 mm |

General

| | |
|------|--|
| Note | Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in |
| | Do not plug in while the power is connected |

Test adapter - PAIS-4-FIX BU - 3032798

Technical data

General

| | |
|-------|---|
| | Latching testing accessories, therefore only suitable for being plugged in once |
| Color | blue |

| | |
|---------------------------------|-------------------|
| Material | Copper alloy |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Max. voltage | 250 V |
| Maximum load current | 10 A |
| Insertion/withdrawal cycles | 1 |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141148 |
| eCl@ss 4.0 | 27141127 |
| eCl@ss 4.1 | 27141127 |
| eCl@ss 5.0 | 27141127 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141148 |
| eCl@ss 8.0 | 27141148 |
| eCl@ss 9.0 | 27141148 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC002255 |
| ETIM 5.0 | EC002255 |
| ETIM 6.0 | EC002555 |
| ETIM 7.0 | EC002555 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121411 |
| UNSPSC 12.01 | 39121411 |
| UNSPSC 13.2 | 20122006 |

Test adapter - PAIS-4-FIX BU - 3032798

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 18.0 | 20122006 |
| UNSPSC 19.0 | 20122006 |
| UNSPSC 20.0 | 20122006 |
| UNSPSC 21.0 | 20122006 |

Approvals


Approvals


Approvals

EAC / EAC

Ex Approvals

Approval details

| | | |
|-----|---|--------------------------|
| EAC |  | RU C- DE.A*30.B.01742 |
|-----|---|--------------------------|

| | | |
|-----|---|--------------------------|
| EAC |  | RU C- DE.BL08.B.00511 |
|-----|---|--------------------------|